

Minicom PX USB - Remote KVM access with Power-on-Cable (POC)

MODEL NUMBER: 0SU70068



Description

Complete access to your computer - any time, anywhere

Completing the OOB Remote Support package

Virtual Media capability for each server

Complete remote support for mission critical applications

Scalable centralized management

Features

- Single port, palm-sized device
- Virtual Media for complete remote management
- Absolute Mouse Support for reduced installation hassle
- BIOS level access over IP connection
- Management system enabled
- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers

Highlights

- Single port, palm-sized device
- Virtual Media for complete remote management
- Absolute Mouse Support for reduced installation hassle
- BIOS level access over IP connection
- Management system enabled
- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers
- Power over Ethernet & external power option
- Includes one Power-on-Cable (POC) - Model #0SU60020
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- Compatible with Windows 98 and higher, Novell, Linux, SUN Solaris and Mac

Resolution

- Host Computer: Supports video resolutions up to 1600 x 1200 @ 85Hz
- Client Computer: Recommended - client computer resolution should be higher than resolution on the host computer

Package Includes

- PX USB
- Power-on-Cable (POC)
- USB Cable Kit
- Rackmount Hardware
- Owner's Manual



Powering Business Worldwide



- Power over Ethernet & external power option
- Includes one Power-on-Cable (POC) - Model #0SU60020
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	654518212174
CONNECTIONS	
Number of Ports	1
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / in.)	7.50 x 7.20 x 1.50
Shipping Dimensions (hwd / cm)	19.05 x 18.29 x 3.81
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	3.3 x 1.05 x 8
Unit Weight (lbs.)	0.66
Unit Weight (kg)	0.30
ENVIRONMENTAL	
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Relative Humidity	80% Non-Condensing
Operating Temperature	0°C to 40°C / 32°F to 104°F
COMMUNICATIONS	
IP Remote Access	No
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.