



Powering Business Worldwide



# Protect It! Surge Suppressor - 6 German CEE 7 Schuko AC outlets

MODEL NUMBER: **161379T**

## Description

Tripp Lite's SurgeBlocker 16-1379T offers economical AC surge suppression for full protection of 220-240V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. SurgeBlocker 16-1379T offers 6 German CEE 7 Schuko output receptacles and 3 meter AC line cord. AC suppression rated at 330 joules shields equipment from surges and line noise. Attractive white suppressor housing. Lifetime warranty.

PLUG/OUTLETS: Input: German CEE 7 Schuko Plug/Output: 6 CEE 7 Receptacles/3m AC line cord

ELECTRICAL: 220-240V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 300V RMS Clamping/330 joules

## Highlights

- 6 CEE7 (German) outlets
- 3 m power cord
- 330 joule rating
- Lighted power switch

## Package Includes

- 16-1379T AC surge suppressor
- Instruction manual and warranty information

## Features

- SurgeBlocker 16-1379T offers economical AC surge suppression
- 330 joules AC surge suppression shields equipment from surges and line noise
- 6 German CEE 7 Schuko AC outlets protect computers and peripherals
- 3m AC line cable
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LED confirms surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- Lifetime warranty

## Specifications

OVERVIEW	
UPC Code	037332221209
INPUT	
Voltage Compatibility (VAC)	220-250
Input Plug Type	Schuko
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	10



Powering Business Worldwide



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch controls power to all outlets
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	330
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Unit Dimensions (hwd / in.)	2.6 x 2.6 x 14
Unit Dimensions (hwd / cm)	6.5 x 6.5 x 35.5
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.