

Component Video Gold Cable (3xRCA M/M), 6 ft. (1.83 m)

MODEL NUMBER: **A008-006**



Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium grade 99.99% pure solid copper coaxial conductors with Silver Plating
- True 75ohm impedance for widest bandwidth
- 6-cut, RCA connector, with split tip center pin, ensures a precise connection
- Gold plating resists corrosion and provides increased durability
- Color coded connectors for easy identification
- Abrasion resistant flexible PVC jacket

Specifications

OVERVIEW	
UPC Code	037332121820
Technology	Component
CONNECTIONS	
Side A - Connector 1	(3) RCA (MALE)
Side B - Connector 1	(3) RCA (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Length (ft.)	6

Highlights

- Constructed of high quality, 99.99% pure solid copper coaxial cable with silver plating for best high frequency response
- 75 ohm impedance for maximum bandwidth
- Double-shielded construction provides superior protection against EMI/RFI
- Excellent noise isolation with 100% aluminum foil/braid shielding

System Requirements

- Home theater equipment with RCA digital audio/video connectors

Package Includes

- 6 ft. Component Video Gold Cable



Powering Business Worldwide



Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	0.64
Shipping Weight (kg)	0.29
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.