

S-Video Gold Cable (MD4 M/M), 12-ft.

MODEL NUMBER: A012-012



Highlights

- Constructed of high quality , 99.99% pure solid copper conductors
- True 75 ohm impedance for maximum bandwidth
- Double-shielded construction provides superior protection against EMI/RFI
- Excellent noise isolation with 100% aluminum mylar foil/braid shielding

System Requirements

- Home theater equipment with S-Video connectors

Package Includes

- 12 ft. S-Video Gold Cable

Description

Tripp Lite's Premium S-Video Gold Cable offers superior video quality, resulting in brighter, more saturated colors, and sharper images. S-Video separates brightness from color, using two separate coaxial conductors to create clean, accurate signals.

Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium grade, 99.99% pure copper conductors
- 24KT Gold precision machined connector provides solid contact and resistance to corrosion
- Double shielding ensures maximum protection against electromagnetic and radio frequency interference

Specifications

| OVERVIEW | |
|--------------------------------|----------------|
| UPC Code | 037332121868 |
| Technology | S-Video |
| CONNECTIONS | |
| Side A - Connector 1 | S-VIDEO (MALE) |
| Side B - Connector 1 | S-VIDEO (MALE) |
| Latching or Gripping Connector | No |
| PHYSICAL | |
| Color | Black |
| Cable Length (ft.) | 12 |
| Cable Length (m) | 3.66 |



Powering Business Worldwide



| | |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / in.) | 10.00 x 8.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 25.40 x 20.32 x 1.27 |
| Shipping Weight (lbs.) | 0.38 |
| Shipping Weight (kg) | 0.17 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.