

RG59 Coax Cable with F-Type Connectors, 6 ft. (1.83 m)

MODEL NUMBER: A200-006



Highlights

- Double Shielded RG59 Coax
- Gold Plated screw type F connectors
- Fully molded ends ensure long life use

Package Includes

RG59 Coax cable with F-Type Connectors - 6-ft. (1.83 m)

Features

- Double Shielded (Foil and Braid) RG59B/U Cable
- 24K Gold Plated screw type F connectors
- Fully molded ends ensure long life use
- Use with Cable or Satellite Receivers, VCR, DVD, Coax enabled TV

Specifications

OVERVIEW	
UPC Code	037332146670
Technology	Coax; RG59/RG6
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	F-TYPE (MALE) THREADED COAX
Side B - Connector 1	F-TYPE (MALE) THREADED COAX
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.