

## RG59 Coax Cable with F-Type Connectors, 12 ft. (3.66 m)

MODEL NUMBER: A200-012



### Highlights

- Double Shielded RG59 Coax
- Gold Plated screw type F connectors
- Fully molded ends ensure long life use

### Package Includes

RG59 Coax cable with F-Type Connectors - 12-ft. (3.66 m)

### Features

- Double Shielded (Foil and Braid) RG59B/U Cable
- 24K Gold Plated screw type F connectors
- Fully molded ends ensure long life use
- Use with Cable or Satellite Receivers, VCR, DVD, Coax enabled TV

## Specifications

OVERVIEW	
UPC Code	037332146663
Technology	Coax; RG59/RG6
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	F-TYPE (MALE) THREADED COAX
Side B - Connector 1	F-TYPE (MALE) THREADED COAX
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	12
Cable Length (m)	3.66



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 7.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 17.78
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.