



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: AV810

8-Outlet Premium Protection Audio/Video Surge Suppressor



Highlights

- 8 outlets / 10-ft. cord with space saving right angle plug
- 3240 joule rating
- 2-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-line tel/modem surge protection
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only)

Description

Tripp Lite's AV810 Gold Series Audio Video Surge / Spike Suppressor provides high performance protection (3240 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to the heaviest transient surges. Two pairs of HD 2.2 Ghz coax line suppression jacks protect any two type F coax lines for cable-TV, satellite, broadcast antenna or cable modems. 1 set of RJ11 jacks offers surge suppression for pay-per-view HD satellite systems, dial-up and DSL modems. The AV810 offers 8 total outlets, 10-foot cord with space-saving angled plug and diagnostic LEDs with audible alarm to warn of wiring problems and suppressor damage. Integrated child-safety outlet covers safely seal off unused outlets. Black high impact plastic housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of Audio Video systems. \$250,000 Ultimate Lifetime Insurance (USA & Canada only).

Applications

Gold Series Premium performance Surge/Spike protection Perfect for small Audio Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more.

Package Includes

- AV810 Gold Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	

Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15
Outlet quantity / type	8 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Single row of 5, plus a second row of 3 for transformer accommodation
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input plug features	Space-saving right-angle input plug
Input cord length (ft.)	10
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	3240 joules
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	330/400/400
EMI / RFI filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1
Cable (Coax) Protection Details	1
PHYSICAL	
Shipping weight (lbs)	2.18
Unit Dimensions (HWD/in)	4.86 x 9.55 x 1.51
Shipping Dimensions (HWD/in)	11.41 x 8.66 x 2.04
Unit weight (lbs)	2.02
Material of construction	Plastic

Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Attractive black color scheme
AC line cord color	black
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance (Lifetime product warranty)
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4137.