



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: AVBAR10

10-Outlet Ultimate Protection Isobar Audio/Video Surge Suppressor

Highlights

- 10 outlets / 8-ft. cord with space saving right angle plug
- 3384 joule rating
- Isolated Filter Banks
- 3-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-Ethernet RJ45 surge protection jack
- 1-line tel/modem surge protection
- All-metal housing
- \$500,000 Ultimate Lifetime Insurance (USA and Canada only)



Description

Tripp Lite's AVBAR10 Platinum Series Isobar Audio Video Surge / Spike Suppressor provides premium protection (3384 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for any Audio/Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 8 outlets (widely spaced outlets accommodate up to 4 transformers and plug-in safety covers), 3-line HD 2.2 Ghz coaxial protection, 1-Ethernet RJ45 surge protection jack and 1-line tel/modem protection safeguard an entire A/V system. \$500,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes all-metal housing, three diagnostic LEDs (Line OK, Grounded & Protected) and 8-ft. cord with a right-angle plug. Additional accessories include; 8-ft. coaxial cable, 6 ft. network cable and 6-ft. phone cord.

Applications

Platinum Series Premium performance Surge/Spike protection Perfect for medium Audio Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more.

Package Includes

- AVBAR10 Platinum Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. network cable
- 6 ft. phone cord
- Instruction manual with warranty information

Features

- 3384 joules surge / spike suppression protection rating
- EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Isolated Filter Banks eliminate interference between connected components

- All-metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an Audio / Video system
- \$500,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- Widely spaced outlets accommodate up to 4 transformers
- Four plug-in safety covers protect against accidental contact
- 3 sets of surge-protected Type F gold HD 2.2 GHZ coaxial connectors (with included 6-ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 1-Ethernet RJ45 surge protection jack (with included 6-ft. network cable) safeguards router & network
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (Satellite, PVRs) on a single dial-up line.
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a Audio Video system
- 3 diagnostic LEDs alert user to protection, line power and fault status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- UL and cUL listed, RoHS compliant
- \$500,000 Ultimate Lifetime Insurance (Lifetime product warranty)

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1440
Circuit Breaker (amps)	12
Outlet quantity / type	10 NEMA 5-15R
Transformer accommodation	Accommodates 2 transformers
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input plug features	Space-saving right-angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	150000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm line power, protection and ground status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	3384
AC suppression response time	NM = instantaneous CM = < 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression

Clamping voltage (RMS)	140V
EMI / RFI filtering	Up to40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	Yes
Network (Ethernet) Protection Details	1 line
PHYSICAL	
Unit Dimensions (HWD/in)	14.25 x 2.25 x 3.5
Unit weight (lbs)	3.5
Material of construction	metal
Integrated keyhole mounting tabs	Keyhole mounting slots allow desk or wall mounting
Housing Color	Attractive black color scheme
AC line cord color	black
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4134.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.