



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: AVBAR6

6-Outlet Ultimate Protection Isobar Audio/Video Surge Suppressor

Highlights

- 6 outlets / 6-ft. cord with space saving right angle plug
- 2784 joule rating
- Isolated Filter Banks
- 2-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-line tel/modem surge protection
- All-metal housing
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only)



Description

Tripp Lite's AVBAR6 Platinum Series Isobar Audio Video Surge / Spike Suppressor provides premium protection (2784 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium Audio/Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 6 outlets (widely spaced outlets accommodate up to 2 transformers and plug-in safety covers), 2-line HD 2.2 Ghz coaxial protection and 1-line tel/modem protection safeguard an entire A/V system. \$250,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes all-metal housing, three diagnostic LEDs (Line OK, Grounded & Protected) and 6-ft. cord with a right-angle plug. Additional accessories include; 6-ft. coaxial cable and 6-ft. phone cord.

Applications

Platinum Series Premium performance Surge/Spike protection. Perfect for small-to-medium Audio Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more.

Features

- 2784 joules surge / spike suppression protection rating
- EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Isolated Filter Banks eliminate interference between connected components
- All-metal housing safely withstands the strongest surges
- 6 surge-protected NEMA 5-15R AC outlets safeguard an Audio / Video system
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- Widely spaced outlets accommodate up to 2 transformers
- Four plug-in safety covers protect against accidental contact
- 2 sets of surge-protected Type F gold HD 2.2 GHZ coaxial connectors (with included 6-ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (Satellite, PVRs) on a single dial-up line.
- 6-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a Audio Video system
- 3 diagnostic LEDs alert user to protection, line power and fault status

- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- UL and cUL listed, RoHS compliant
- Lifetime product warranty

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output volt amp capacity (amps)	12
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Accommodates 2 transformers
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	6
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and illuminated 2-position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm line power, protection and fault status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2784 joules
AC suppression response time	NM = instantaneous CM = < 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	140V
UL1499 let through rating	330V - UL verified
EMI / RFI filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1
Cable (Coax) Protection Details	1
PHYSICAL	
Unit Dimensions (HWD/in)	2.5 x 9 x 3.5

Shipping Dimensions (HWD/in)	3 x 11.5 x 7
Unit weight (lbs)	2.8
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting slots allow desk or wall mounting
Housing Color	Attractive black color scheme
AC line cord color	Black
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
WARRANTY	
Standard warranty period	\$250,000 Ultimate Lifetime Insurance (Lifetime product warranty)
Connected equipment insurance (USA, Canada, Puerto Rico)	\$250,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4136.