

230V Automatic Voltage Switch with Surge Protection, 190 Joules, Direct Plug-In

MODEL NUMBER: AVS5D



Highlights

- Direct plug-in / 1 outlet
- Over- and undervoltage protection
- Surge and spike protection
- 5-amp current rating

Package Includes

- AVS5D Automatic Voltage Switch
- Owner's Manual

Description

AVS5D Automatic Voltage Switch is a power protection device combining overvoltage, undervoltage and spike/surge protection for your appliances and electronics. This device also guards against surges and spikes that may occur when power is restored. The AVS5D easily handles small refrigerators, small freezers, small air conditioners, TVs and computer equipment, plugged into its single outlet, from fluctuating power.

Program buttons let you quickly set voltage range, on/off delay, overload protection and digital display mode. The easy-to-read digital LED displays show you voltage, wattage, settings and status at a glance. The AVS5D features surge-protecting components to guard against spikes and surges.

Features

- 5-amp current rating
- BS 1363 UK plug
- BS 1363 UK outlet
- Program buttons
- Voltage LED
- Load LED
- Digital LED display

Specifications

OVERVIEW	
UPC Code	037332182197
INPUT	
Nominal Input Voltage(s) Supported	220V AC
Recommended Electrical Service	230V



Powering Business Worldwide



Voltage Compatibility (VAC)	230
Maximum Surge Amps	4500kA
Input Plug Type	BS1363
Input Cord Details	Direct Plug-In
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) British BS 1363A
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	190
AC Suppression Response Time	<1ns
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Material of Construction	Plastic
Mounting Holes or Slots	No
Receptacle Color	White
Shipping Dimensions (hwd / in.)	5.31 x 3.38 x 2.60
Shipping Dimensions (hwd / cm)	13.49 x 8.59 x 6.60
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	5.200 x 2.520 x 1.880
Unit Dimensions (hwd / cm)	13.21 x 6.40 x 4.78



Powering Business Worldwide



FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.