



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: AVSWIV6

### 6-Outlet (Swivel) Advanced Protection Isobar Audio/Video Surge Suppressor



#### Highlights

- 6 outlets 2 banks rotates 90 degrees to accommodate all types of plugs.
- Direct plug-in design
- 2100 joule rating
- 1-line HD gold coax (2.2GHz bandwidth) protection
- 1 line tel/modem protection
- Lifetime product warranty (U.S., Canada & Puerto Rico)
- \$50,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's AVSWIV6 Low-Profile Audio Video Surge Suppressor provides high-performance protection (2100 joules) stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small Audio Video installations: high-definition Flat Panel TVs, satellite and A/V receivers, DVD/CD players and more. 6 outlets, 2 banks of three rotates 90 degrees to accommodate all types of plugs. 1-line HD 2.2 Ghz coaxial protection and 1-line tel/modem protection. \$50,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes two diagnostic LEDs (confirm "protected" and "grounded" status) and 6 ft. coaxial cable and 6 ft. phone cord.

#### Applications

Gold Series performance Surge/Spike protection. Perfect for Flat Panel high-definition video displays small Audio Video installations:, HD Cable / HD satellite sources and HTiB, DVD/CD players and more.

#### Package Includes

- AVSWIV6 Gold Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

#### Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120V AC
OUTPUT	
Frequency compatibility	50 / 60 Hz

Output watts	1440
Output volt amp capacity (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Rotatable
<b>INPUT</b>	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input cord length (ft.)	Direct plug in
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	2100 joules
AC suppression response time	NM = instantaneous CM = < 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
UL1499 let through rating	400,400,500
EMI / RFI filtering	Up to 40 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1
Cable (Coax) Protection Details	1
<b>PHYSICAL</b>	
Shipping weight (lbs)	1
Unit Dimensions (HWD/in)	6.25 x 4 x 2.25
Shipping Dimensions (HWD/in)	8.60 x 5.80 x 2.38
Unit weight (lbs)	.6
Material of construction	Plastic
Housing Color	Black
<b>CERTIFICATIONS</b>	
UL1449 1998 Rev. (AC Suppression)	UL1449 3rd EDITION
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance (Lifetime product warranty)

**Connected Equipment  
Insurance (U.S., Canada &  
Puerto Rico)**

\$50,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4138](http://www.tripplite.com/en/products/model.cfm?txtModelID=4138).

---

© 2010 Tripp Lite. All Rights Reserved.