



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: AVSWIV6

6-Outlet (Swivel) Advanced Protection Isobar Audio/Video Surge Suppressor



Highlights

- 6 outlets 2 banks rotates 90 degrees to accommodate all types of plugs.
- Direct plug-in design
- 2100 joule rating
- 1-line HD gold coax (2.2GHz bandwidth) protection
- 1 line tel/modem protection
- Lifetime product warranty (U.S., Canada & Puerto Rico)
- \$50,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Description

Tripp Lite's AVSWIV6 Low-Profile Audio Video Surge Suppressor provides high-performance protection (2100 joules) stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small Audio Video installations: high-definition Flat Panel TVs, satellite and A/V receivers, DVD/CD players and more. 6 outlets, 2 banks of three rotates 90 degrees to accommodate all types of plugs. 1-line HD 2.2 Ghz coaxial protection and 1-line tel/modem protection. \$50,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes two diagnostic LEDs (confirm "protected" and "grounded" status) and 6 ft. coaxial cable and 6 ft. phone cord.

Applications

Gold Series performance Surge/Spike protection. Perfect for Flat Panel high-definition video displays small Audio Video installations:, HD Cable / HD satellite sources and HTiB, DVD/CD players and more.

Package Includes

- AVSWIV6 Gold Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

Features

- 6 rotatable outlets allow for easier plug connection and removal
- 2100 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 1 set of surge-protected Type F gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line

- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- Lifetime warranty with \$50,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only)

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1440
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Rotatable
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
Maximum Surge Amps	75000
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2100
AC suppression response time	NM = instantaneous CM = < 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
UL1499 let through rating	400,400,500
EMI / RFI filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line (2.2 GHz Bandwidth)
PHYSICAL	
Shipping weight (lbs)	1
Unit Dimensions (HWD/in)	6.25 x 4 x 2.25
Shipping Dimensions (HWD/in)	8.60 x 5.80 x 2.38

Unit weight (lbs)	.6
Material of construction	Plastic
Housing Color	Black
Outlets center to center measurement	29mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4138.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.