



Powering Business Worldwide

# KVM Switch - 4-Port Desktop KVM Switch (USB)

MODEL NUMBER: B006-004-R



### Highlights

- USB Connections on both Console and Server side
- P758-Series KVM Cable kit required to connect to a computer
- Push Button switching on the front of the unit
- Built-in 2-Port USB hub shares two USB peripherals between attached systems
- OS independent operation - use with PCs or MACs

### Package Includes

- B006-004-R 4-port USB KVM Switch
- Instruction manual with warranty information

### Description

Tripp Lite's 4-port Desktop USB KVM Switch is the optimal solution for controlling up to 4 USB computers from one keyboard, mouse, and monitor. It features keyboard and mouse emulation for error-free boot-ups and works on all operating systems. This device also supports 180MHz video resolutions up to 1920 x 1440 pixels without any noticeable degradation. It features a compact design that does not require external power, software, or complicated set-up procedures.

### Features

- Control up to 4 USB computers from a single keyboard, mouse and monitor
- Console Ports: HD15 Female (Monitor) and 2 USB A Female (Keyboard/Mouse)
- Computer Ports: 4 HD15 Male (Monitor) and 4 USB B Female (Dual Keyboard/Mouse)
- Includes 2 USB A Female ports for sharing of USB peripherals between connected computers
- 2 LEDs per port; one indicates when the computer is connected & on, the other indicates when the computer has been selected
- Supports 180MHz video resolutions up to 1920 x 1440
- Supports VGA, SVGA, or Multisync monitors
- Does not require external power, software, or complicated set-up procedures
- Select a computer via front panel push-buttons
- Includes autoscan feature
- Keyboard and mouse emulation for dependable computer boot-up
- Compatible with all operating systems
- Compatible with most mice; including scroll mice

## Specifications

OVERVIEW	
UPC Code	037332014962
Console	No



Powering Business Worldwide

Max CPU	4
Product Rear View	B006-004-R-rear.pdf
<b>CONNECTIONS</b>	
Number of Ports	4
Computer/Server Ports - Port 1	HD15 (Male)
Computer/Server Ports - Port 2	USB B (Female)
PC/Server Connections	USB
<b>PHYSICAL</b>	
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	4.00 x 13.00 x 8.50
Shipping Dimensions (hwd / cm)	10.16 x 33.02 x 21.59
Shipping Weight (lbs.)	3.50
Shipping Weight (kg)	1.59
Unit Dimensions (hwd / in.)	2.250 x 9.000 x 6.250
Unit Weight (lbs.)	3
Unit Weight (kg)	1.36
<b>ENVIRONMENTAL</b>	
BTUs	50Hz, 2.7 / 60Hz, 2.4
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons
IP Remote Access	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.