

KVM Console Switch - 8-Port NetDirector 1U Rackmount Console KVM Switch with 15 LCD

MODEL NUMBER: **B020-008**



Description

Tripp Lite's 8-port KVM Console Switch is the optimal solution for controlling multiple computers from one keyboard, mouse and monitor. This single unit combines an 8 port KVM switch, keyboard, 15" LCD monitor and touchpad - all in a mere 1U of rack space. Stores neatly in the rack, pulls out when needed. Control up to 504 computers from this single console by daisy-chaining additional 16 port KVM switches (model B022-016). Easily switch ports using the touchpad with On Screen Display (OSD) or by using the keyboard "hot key" functions. Control PS/2 or USB systems when using the appropriate cable kit.

Features

- Control multiple computers from one keyboard, mouse, and monitor
- Combines an 8 port KVM switch, keyboard , 15" LCD monitor and touchpad in a 1U rack-mount drawer
- Daisy-chain multiple 16 port KVM switches (Model B022-016) in order to control up to 504 computers
- Does not require software or complicated set-up procedures
- Select a port by using the On Screen Display (OSD) and the touchpad or by using the keyboard "hot key" functions
- Offers autoscan feature
- Multi-level password security to ensure only authorized people have access to the connected computers
- 2 LEDs per port; one indicates when the computer is connected & on, the other indicates when the computer has been selected
- PS/2 and USB compatibility by connecting appropriate Tripp Lite cable kit
- Flash upgradeable
- Hot pluggable -- add or remove computers without having to power down the switch
- Auto-sensing of station position on daisy chained installations -- no need for manual DIP switch setting - front panel LED indicates station position
- Port names automatically reconfigured when station sequence is changed
- Console detaches from the switch chassis for easy maintenance
- 15" LCD display supports high XGA resolutions of up to 1024 x 768 with 250cd/m(sq) brightness
- Power Consumption: 120V 60Hz 22.8W/230V 50Hz 24W

Highlights

- Entire network control system in just 1U rack space -- includes keyboard, 15" LCD screen, touch pad and 8-port switching capability
- Two levels of password protection (administrator/user)
- Flash upgradeable firmware
- Daisy-chain additional B022-016 KVM switches to control up to 504 servers
- "Super Flex" 3-in-1 cables make cable management a breeze

System Requirements

- PS/2 mouse (or a USB mouse with USB-to-PS/2 adapter)
- PS/2 keyboard (or a USB or AT keyboard with a PS/2 adapter)
- PS/2 computer (or a Mac, Sun or USB computer with appropriate adapter).
- 1 P774-006, P774-010, P774-015

Package Includes

- 8 Port KVM Switch
- AC Power Cord (C13 Receptacle to 5-15P Plug)
- Instruction manual
- Firmware Upgrade Cable
- (2) PS/2 Cable Kits

Specifications

OVERVIEW	
UPC Code	037332121134
Console	Yes
Max CPU	504
CONNECTIONS	
Number of Ports	8
PC/Server Connections	USB; PS/2; VGA
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	6.00 x 23.75 x 35.25
Shipping Dimensions (hwd / cm)	15.24 x 60.32 x 89.54
Shipping Weight (lbs.)	44.10
Shipping Weight (kg)	20.00
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.