

1U Rack-Mount Console with 19-in. LCD, Short-Depth; TAA Compliant

MODEL NUMBER: **B021-000-19-SH**



Description

The B021-000-19-SH 1U rack-mount console is the ideal solution for specialized vehicle projects, including rescue services and military-specific applications. It can be mounted in as little as a 19-inch-deep rack and features an integrated 19-inch LCD display (max native resolution of 1366 x 768), full 104-key keyboard and touchpad, all in a 1U rack-mountable housing. It also features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc. Your peripheral device connects to the USB-A port on the front of the unit, and your computer connects to the USB-A port on the back of the unit using a UR020-Series M/M cable. This console is designed for use with a server or a KVM switch with PS/2 or USB console connectors. Constructed of heavy-duty steel housing.

Features

- Mounts in 19" to 30" deep cabinets
- Full 19" LCD display screen, 104-key keyboard, touchpad
- Max native resolution of 1366 x 768
- Auto Sensing External AC Adapter, 6-ft. (Input: 100-240V, 50/60Hz, 1.5A)
- Includes 6-ft. PS/2 cable kit for use with PS/2 KVMs or Servers
- PS/2 to USB adapter included for use with USB KVMs or servers
- Features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Single rail, ball bearing slides
- Constructed of heavy-duty steel housing
- Complies with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

Highlights

- Short-depth console mounts in cabinets with a minimum depth of 19"
- Designed for use with KVMs or Servers that have PS/2 or USB connectors
- 19" LCD Screen with max native 1366 x 768 resolution
- Auto Sensing External Power Supply (Input: 100-240V, 50/60Hz, 1.5A)
- TAA compliant for GSA Schedule purchases

Package Includes

- 1U 19" KVM Console Short-Body
- External AC Power Adapter with C14 Socket (Input: 100-240V, 50/60Hz, 1.5A)
- C13 to 5-15P Power Cord - 6-ft.
- PS/2 Cable Kit - 6-ft.
- PS/2 to USB Adapter
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332143853
Technology	PS/2; VGA/SVGA

PRODUCT OVERVIEW	
Product Overview	1U 19" KVM Console Short-Body
VIDEO	
Max Supported Video Resolution	1366 x 768 @ 60Hz
Extended Mode	No
Mirror Mode	No
INPUT	
AC Power Adapter Plug(s)	IEC-320-C14
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
AC Power Adapter Output Specs (V / A)	12V / 2.5A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter with detachable power cord
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A
DC Barrel Plug	OD: 5.5 x 2.5 x 16.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	30
Power Consumption Detail	(Line Mode) 30W / (Standby Mode) 5W
CONNECTIONS	
Number of Ports	1
Daisy-Chain Port	No
Firmware Upgrade Port	No
PC/Server Connections	PS/2; USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (CAPS LOCK, SCROLL LOCK, NUM LOCK)



Powering Business Worldwide



PHYSICAL	
Color	Black
Material of Construction	Steel (Steel, Electrogalvanized, Cold Rolled, Coil)
LCD Monitor (in.)	19
Total Number of Ports	1
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	5.90 x 23.10 x 24.17
Shipping Dimensions (hwd / cm)	14.99 x 58.67 x 61.39
Shipping Weight (lbs.)	34.30
Shipping Weight (kg)	15.56
Unit Dimensions (hwd / in.)	1.750 x 18.750 x 19.000
Unit Packaging Type	Box
Unit Weight (lbs.)	27.13
Unit Weight (kg)	12.31
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.1 BTU/Hr
COMMUNICATIONS	
Hotkey	No
IP Remote Access	No
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
NIAP-Certified Secure	No
Number of Users	1
Driver Required	No
BUILT-IN CONSOLE	
Console Screen Size (inches)	19
Console Screen Aspect Ratio	16:9
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; GS; BSMI; RoHS



Powering Business Worldwide



Product Certifications	EN 60950-1
Product Compliance	RoHS; CE (Europe); REACH; FCC Part 15 Class A (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.