



Powering Business Worldwide

KVM Switch Accessories - IP Remote Access Unit

MODEL NUMBER: **B050-000**



Description

Tripp Lite's B050-000, IP Remote Access Unit, offers convenient and economic remote KVM access and control via LAN or Internet. It captures, digitizes, and compresses video data and transmits them, with keyboard and mouse signals, to and from a remote computer; work from anywhere in the office, remote locations, or from home! The B050-000 provides a non-intrusive solution for both remote access and control. The remote access and control software runs on its embedded processors only, but not on mission-critical servers, so that there is no interference with server operation or even impact on the network performance.

The B050-000 may be accessed using a standard Java enabled web browser. You may use the HTTP protocol, or, a secure encrypted connection via HTTPS. Just enter the configured IP address of the B050-000 into your web browser. There is only one user who has unrestricted access to all of the B050-000 features. The unit also features Lightweight Directory Access Protocol (LDAP) support, an application protocol for querying and modifying directory services running over TCP/IP.

Features

- KVM access (keyboard, video, mouse) over IP or analog telephone line
- Works with Microsoft Internet Explorer 5.0 or higher
- Senses video resolution automatically for the best possible screen capture
- High-Performance mouse tracking and synchronization
- Features 256-bit SSL encrypted security
- Additional port to connect a local user console for direct analog access to the KVM switch
- Flash - upgradeable firmware
- Supports SNMP and LDAP
- Compact size: 3.75"L x 1"H x 2.75"H

Specifications

OVERVIEW	
UPC Code	037332121530

Highlights

- Remotely control your servers via LAN, WAN, or the Internet
- Works with most KVM switches
- Compact and Lightweight - takes up no rack-space

System Requirements

- PS/2 KVM Switch
- Internet Explorer 5.0 or higher
- Java enabled web browser

Package Includes

- 1 - B050-000 Base unit w/CD-ROM
- 1 - External Power supply
- 2 - KVM cable kits
- 1 - Null Modem Cable
- 1 - Quick Start Guide
- 1 - Owner's Manual CD



Powering Business Worldwide

Accessory Type	Remote Control Module
Accessory Class	KVM Switch Accessories
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.2A Output: 5V, 1.6A
CONNECTIONS	
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	(x2) MiniDIN6 (Male)
Included KVM Cable (Equipment Side) - Connector 3	USB A (Male)
Included KVM Cable (Equipment Side) - Connector 4	DB9 (Male)
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.00 x 9.50 x 15.00
Shipping Dimensions (hwd / cm)	10.16 x 24.13 x 38.10
Shipping Weight (lbs.)	4.60
Shipping Weight (kg)	2.09

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.