

KVM Switch - 32-Port (4-User) 1U Rackmount Cat5 Matrix KVM Switch

MODEL NUMBER: **B060-032**



Description

Tripp Lite's 32-port NetDirector® 1U Rackmount Matrix KVM Switch is the optimal solution for controlling multiple computers (combination of PS/2, USB, or Sun) by four independent, simultaneous users. A single unit occupies a mere 1U of rack space, yet can control up to 32 computers. A maximum of 2,048 computers can be connected through a combination of daisy-chaining and cascading. RJ45 connections allow signals to travel up to 150 meters away (500ft), using ordinary Cat5 cable, while maintaining video resolution. Use either PS/2 or USB console equipment to connect to PS/2, USB, or SUN Servers. For Government purchasers, B060-032 is Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Three Level password security: Super Administrator, Administrator, and Users
- Superior video quality - up to 1024 x 768 @ 60Hz at 500ft.
- Auto Signal Compensation (ASC) assures optimum video resolution for distances up to 500ft between the switch and the consoles or computers - no dip switch setting required
- PS/2 keyboard and mouse emulation - computers boot even when the console focus is elsewhere. Keep Alive feature ensures that the keyboard and mouse work properly even if the switch temporarily loses power
- Daisy chain up to 7 additional B060-032 KVM Switches
- Cascade up to 32 B060-032 KVM switches from each station on the chain
- Up to 2,048 computers on a daisy chained/cascaded installation
- No software required; convenient computer selection via intuitive hotkey combinations or On Screen Display (OSD) menus
- OSD port list automatically expands when stations are added - port names are automatically reconfigured when the station sequence is changed
- OSD screen automatically adjusts to resolution changes
- Hot pluggable; add or remove components without having to power off the switch
- USB & PS/2 Consoles can control any combination of USB, PS/2, or SUN computers
- LCD, VGA, SVGA, XGA, and MultiSync support; DDC2B
- Rackmount Hardware Included
- Lifetime firmware upgrading via flash ROM

Highlights

- Four consoles independently and simultaneously control up to 32 directly connected computers, or over 2,000 when additional KVM's are connected
- Multi-Platform support: PC, Sun, or Mac
- Rackmountable in a 1U design, with 32 available ports...Rackmount Hardware Included
- Inexpensive Cat5 cabling makes cable management a breeze; 500ft distance from Console to switch, or 500ft from Switch to Servers
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Console: The Tripp Lite B062-002-PS2 or B062-002-USB Console Interface Module must be used to connect a console (Keyboard, Monitor and Mouse) to the KVM switch
- Computers: The Tripp Lite B054-001-SUN, B054-001-PS2 or B054-001-USB Server Interface Module must be used to connect a computer/server to the KVM switch

Package Includes

- 1 - B060-032 KVM Switch
- 1 - Power Cord
- 1 - Daisy Chain Cable
- 1 - CD with Owner's Manual
- 1 set - Rackmount Hardware



Powering Business Worldwide



- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332123008
Console	No
Max CPU	2048
CONNECTIONS	
Number of Ports	32
PC/Server Connections	USB; PS/2; VGA
PHYSICAL	
Color	Black
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	5.50 x 20.00 x 13.00
Shipping Dimensions (hwd / cm)	13.97 x 50.80 x 33.02
Shipping Weight (lbs.)	12.20
Shipping Weight (kg)	5.53
ENVIRONMENTAL	
BTUs	38.9 to 41.7
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
Number of Users	4

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.