

HDMI Splitter, 2-Port

MODEL NUMBER: B118-302-R



Description

Tripp Lite's HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device, to be displayed on multiple HDMI or DVI-D Single Link monitors. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Up to 32 displays can be connected by cascading up to three levels of additional splitters. Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the splitter; up to 25 ft. (7.62 m.) between the splitter and a monitor. Splitters can be located up to 100 ft. away from the source using a combination of Tripp Lite long length HDMI cables (P568-050, P568-100-HD) and a HDMI Signal Booster (B122-000-60 or B123-001-60). Includes mounting hardware that allows the unit to be wallmounted, rackmounted or pole mounted. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Supports 3D, Lip-Sync Pass Through, and CEC Pass Through
- Connects to both HDMI and DVI-D Single-Link displays
- Cascade up to three levels of splitters to support up to 32 displays
- Includes mounting hardware that allows the unit to be wallmounted, rackmounted, or pole mounted
- Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the switch; up to 25 ft. (7.62 m.) between the switch and a monitor
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- HDCP compliant
- Connects to both HDMI and DVI-D Single-Link displays
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 16 ft. (5 m.), unless using a signal booster (B122-000-60 or B123-001-60)
- The cable connecting the splitter to a HDMI monitor must be no longer than 25 ft. (7.62 m.)

Package Includes

- B118-302-R 2-Port HDMI Splitter
- 1 ft. HDMI cable
- Mounting hardware
- External Power Supply (Input: 100-240V, 50/60Hz, 0.4A Output: 5V, 2A)
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332144157



Powering Business Worldwide



Technology	HDMI
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.4A; Output: 5V, 2A, 4.9ft
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.12 x 7.25 x 6.50
Shipping Dimensions (hwd / cm)	5.40 x 18.42 x 16.51
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.