

HDMI Splitter, 4-Port

MODEL NUMBER: B118-304-R



Description

Tripp Lite's HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device, to be displayed on multiple HDMI or DVI-D Single Link monitors. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Up to 64 displays can be connected by cascading up to three levels of additional splitters. Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the splitter; up to 25 ft. (7.62 m.) between the splitter and a monitor. Splitters can be located up to 100 ft. away from the source using a combination of Tripp Lite long length HDMI cables (P568-050, P568-100-HD and a HDMI Signal Booster B122-000-60 or B123-001-60). Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Supports 3D, Lip-Sync Pass Through, and CEC Pass Through
- Connects to both HDMI and DVI-D Single-Link displays
- Cascade up to three levels of splitters to support up to 64 displays
- Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the switch; up to 25 ft. (7.62 m.) between the switch and a monitor
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Connects to both HDMI and DVI-D Single-Link displays
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 16 ft. (5 m.), unless using a signal booster (B122-000-60 or B123-001-60)
- The cable connecting the splitter to a HDMI monitor must be no longer than 25 ft. (7.62 m.)

Package Includes

- B118-304-R 4-Port HDMI Splitter
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332143747
Technology	HDMI



Powering Business Worldwide



POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A 4.9ft
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(4) HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.20 x 8.30 x 6.60
Shipping Dimensions (hwd / cm)	5.59 x 21.08 x 16.76
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.