

2x2 HDMI Matrix Switch with Remote Control - 1080p @ 60 Hz (HDMI 2xF/2xF), TAA

MODEL NUMBER: B119-2X2



Connect 2 HDMI source devices to 2 HDMI displays and either share video on both or switch between them.

Description

The B119-2X2 is a 2x2 HDMI Matrix Switch that routes high-definition video from any two HDMI sources to any two HDMI displays. It supports computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p at 60 Hz. The 2x2 Matrix eliminates the need to disconnect and reconnect HDMI sources. It works with any HDMI source that connects to an HDMI display, and each source is accessible at all times by any display by selecting it with an IR remote or using the RS-232 port to switch the unit. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Share multiple HDMI sources between multiple monitors (2 Input, 2 Output)
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Switch between inputs via pushbuttons, remote control, or RS-232 serial
- Monitors can be located up to 25 ft. from the switch
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz
- HDCP and EDID compatible
- Mounting hardware included
- Plug-and-play; No software or drivers required
- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Share multiple HDMI sources between multiple monitors
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz
- Plug-and-play; No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B119-2X2 Local Transmitter Unit
- External Power Supply with NEMA 1-15P Plug(Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- 3.5 mm to DB9 Adapter Cable
- Mounting Hardware
- Remote Control
- Owner's Manual

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332180186 |
| Technology | HDMI; IR |

| VIDEO | |
|---|--|
| Supported Resolutions | 1920x1080 (1080p) |
| HDR Support | Yes |
| INPUT | |
| AC Power Adapter Plug(s) | NEMA 1-15P North America |
| AC Power Adapter Input Specs (V / Hz / A) | 100-240V / 50/60Hz / 0.5A |
| AC Power Adapter Output Specs (V / A) | 5V / 2A |
| AC Power Adapter Cord Length (ft.) | 4.0 |
| AC Power Adapter Cord Length (m) | 1.2 |
| POWER | |
| Power Source Type | AC Adapter |
| AC Adapter | Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A |
| CONNECTIONS | |
| Number of Ports | 2 |
| Side A - Connector 1 | (2) HDMI (FEMALE) |
| Side B - Connector 1 | (2) HDMI (FEMALE) |
| Input x Output | 2 x 2 |
| PHYSICAL | |
| Color | Black |
| Included Mounting Accessories | Yes |
| Rackmountable | Yes |
| Shipping Dimensions (hwd / in.) | 10.24 x 2.17 x 6.46 |
| Shipping Dimensions (hwd / cm) | 26.01 x 5.51 x 16.41 |
| Shipping Weight (lbs.) | 1.50 |
| Shipping Weight (kg) | 0.68 |
| Unit Dimensions (hwd / in.) | 1.200 x 9.200 x 3.900 |
| Unit Dimensions (hwd / cm) | 3.05 x 23.37 x 9.91 |
| Unit Weight (lbs.) | 1.45 |
| Unit Weight (kg) | 0.66 |
| COMMUNICATIONS | |
| Port Control | Push Buttons |



Powering Business Worldwide



| | |
|-------------------------------------|----------------------------|
| Signal Range (ft.) | 60 |
| Signal Range (m) | 18 |
| IP Remote Access | Yes |
| EDID Compatible | Yes |
| IR Remote Extension Support | Yes |
| RS-232 Serial Extension Support | Yes |
| STANDARDS & COMPLIANCE | |
| Product Compliance | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.