

# VGA over Cat5/Cat6 Transmitter and Receiver with Repeater Kit, Box-Style, 1920x1440 60 Hz, Up to 1000 ft. (305 m), TAA

MODEL NUMBER: B130-111



## Features

- Kit comes with both local transmitter and remote/repeater units.
- Locate multiple monitors at different points in a chain of up to 2,000 ft. by connecting additional receiver (B132-100-1 or B132-100-WP-1) or repeater B132-110A) units
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing video to up to 4 remote displays
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Extend a 1920 x 1440 (60Hz) signal up to 500 ft., or a 1024 x 768 (60Hz) signal up to 1,000 ft., between the local transmitter and the first remote/repeater in the installation.
- Extend a 1920 x 1440 (60Hz) signal up to an additional 500 ft., or a 1024 x 768 (60Hz) signal up to an additional 1,000 ft., from the first remote/repeater unit to the last display in the installation.
- Features built-in Equalization and Gain controls for video image adjustment.
- Includes mounting hardware that allows wall mounting, rackmounting or pole mounting.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Highlights

- Kit comes with both local transmitter and remote/repeater units
- Locate multiple monitors at different points in a chain of up to 2,000 ft. by connecting additional receiver (B132-100-1 or B132-100-WP-1) or repeater B132-110A) units
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing video to up to 4 remote displays
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## System Requirements

- Computer with VGA video output
- Monitor / TV with VGA video input

## Package Includes

- B130-111 local transmitter unit
- B130-111 remote/repeater unit
- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.)
- Screwdriver for video adjustment
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332161604
Product Type	Extender Kit
Technology	VGA/SVGA; Cat5/5e; Cat6



Powering Business Worldwide



<b>VIDEO</b>	
Max 720P Range (ft)	500
Max 1080P Range (ft)	500
HDR Support	No
3D Video Supported	No
Maximum Signal Range (ft)	1000
Maximum Signal Range (m)	305
<b>INPUT</b>	
Bus Powered	No
<b>POWER</b>	
Power Over Cable (PoC) Support	No
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	(2) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Number of Displays	1
Form Factor/Mounting Options	Box
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 8.40
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 21.34
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	1000
Max 480P Range (ft)	1000
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500



Powering Business Worldwide



Max 1920 x 1440 Range (ft)	500
Max 480i Range (ft)	1000
Max 640 x 480 Range (ft)	1000
Max 800 x 600 Range (ft)	1000
Max 1600 x 1200 Range (ft)	500
EDID Compatible	No
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
USB Extension Support	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
Driver Required	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.