

## 4-Port VGA with Audio over Cat5 / Cat6 Extender Splitter, Transmitter, 1920x1440 at 60Hz

MODEL NUMBER: B132-004A



### Description

Tripp Lite's B132-004A allows you to split a single VGA Video and Audio signal into 5 (1 local, 4 remote). Increase the number of displays/speakers to up to 25 (1 local, 24 remote) by daisychaining up to six B132-004A units together. Along with a B132-100A or B132-100A-WP-1 remote receiver unit, you can extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6). Support for video resolutions up to 1920 x 1440 (60Hz). For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K. Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted. Up to three B132-004A units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket. Ideal for digital signage situations, such as retail, schools, churches, etc.

### Features

- Splits a single VGA Video and Audio signal into 5 (1 local, 4 remote)
- Increase the number of displays/speakers to up to 25 (1 local, 24 remote) by daisychaining up to six B132-004A units together
- When used with a B132-100A or B132-100A-WP-1 remote receiver unit, you can extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Support for video resolutions up to 1920 x 1440 (60Hz)
- Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted
- Up to three B132-004A units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- Splits a single VGA Video and Audio signal into 5 (1 local, 4 remote)
- Support for video resolutions up to 1920 x 1440 (60Hz)
- Extends a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- 4 Port Extender/Splitter local (Transmitter) unit
- 1 ft. VGA + Audio daisychain cable
- Mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual

## Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332148766
Product Type	Cat5/Cat6 Transmitter
Technology	Stereo Audio; VGA/SVGA
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	3.5MM (FEMALE)
Side B - Connector 1	(4) RJ45 (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.20 x 8.40 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 21.34 x 16.51
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	1.200 x 5.300 x 3.900
Unit Dimensions (hwd / cm)	3.05 x 13.46 x 9.91
Unit Weight (lbs.)	0.85
Unit Weight (kg)	0.39
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.