

Component Video with Stereo Audio over Cat5 Extender Receiver Wallplate

MODEL NUMBER: **B136-100-WP**



Highlights

- Remote extender wallplate for the B136-004 4-Port Extender/Splitter
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Package Includes

- B136-100-WP Component Video + Stereo Audio Remote Extender Wallplate
- 110 Punchdown Tool
- Wallplate Mounting Screws
- Owner's Manual

Description

The B136-100-WP is a remote extender wallplate for the B136-004 4-Port Component Video + Audio Extender/Splitter. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). No external power required.

Features

- Remote extender wallplate for the B136-004 4-port Extender/Splitter
- 110 style punchdown block on back of wallplate....punchdown tool included
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Specifications

| OVERVIEW | |
|-----------------|-------------------------|
| UPC Code | 037332155528 |
| Product Type | Cat5/Cat6 Receiver |
| Technology | Component; Stereo Audio |
| CONNECTIONS | |
| Number of Ports | 1 |



Powering Business Worldwide



| | |
|-------------------------------------|-------------------------|
| Side A - Connector 1 | (5) RCA (FEMALE) |
| Side B - Connector 1 | 110 IDC |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / in.) | 1.10 x 4.90 x 3.00 |
| Shipping Dimensions (hwd / cm) | 2.79 x 12.45 x 7.62 |
| Shipping Weight (lbs.) | 0.35 |
| Shipping Weight (kg) | 0.16 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.