

## DVI Over Cat5 Passive Extender Remote Wallplate

MODEL NUMBER: **B140-1P0-WP**



Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable

### Description

The B140-1P0-WP is a receiver wallplate that is used with the B140-002 and B140-004 extender/splitter transmitter units, and it transmits a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's N202-Series). The B140-1P0-WP is compatible with all operating systems, and is plug and play, with no external power, software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple. Connect a B140-002 or B140-004 transmitter (not included) to a DVI source using a Tripp Lite P561-Series DVI cable (not included). Connect the B140-1P0-WP to a display using a Tripp Lite P561-Series DVI cable (not included). Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 @ 60Hz signal can be extended up to 50 ft. from the source, or a 1024 x 768 @ 60Hz signal up to 100 ft..

### Features

- Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable
- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- HDCP compatible
- Compatible with all operating systems
- Plug and play; no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Highlights

- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Compatible with all operating systems
- Plug and play, no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B140-1P0-WP DVI Over Cat5 Passive Extender Remote Wallplate
- Wallplate screws
- 110 punchdown tool
- Owner's manual



Powering Business Worldwide



## Specifications

OVERVIEW	
UPC Code	037332156662
Product Type	Cat5/Cat6 Receiver
Technology	DVI
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	110 IDC
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
PHYSICAL	
Color	White
Included Mounting Accessories	Yes
Shipping Dimensions (hwd / in.)	2.20 x 7.20 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 18.29 x 16.51
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	11.43 x 6.99 x 2.54
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.