



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: BP240V10RT3U

External Battery Pack and Cable. 3U, Expandable, Black 3-Point Connector

Highlights

- Extends runtime of compatible Tripp Lite UPS Systems with 240VDC external battery connection
- Provides daisy-chain capability
- Simple installation; 3U rackmount, tower or stack adaptable



Description

Tripp Lite's BP240V10RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 3 rack spaces (3U). Upright tower configuration supported with optional 2-9USTAND accessory. Includes heavy gauge cabling with high current DC connectors for simple installation. Additional output connector allows multiple BP240V10RT3U battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SU6000RT3U, SU6000RT3UXR, SU6000RT3UHV, SU10KRT3U, SU10KRT3UHV, SU10K3/1INTPM and other Tripp Lite UPS systems that specify the use of this battery pack.

Applications

- Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems. Additional battery packs may be ordered at time of original UPS purchase or sourced at a later date to extend runtime performance if site power conditions deteriorate and longer battery runtime is desired.

Package Includes

- BP240V10RT3U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 3 rack spaces (3U)
- Supports upright tower installation with optional 2-9USTAND accessory (holds 3 battery packs in tower configuration)
- Set of two input/output connectors allows multiple BP240V10RT3U battery packs to be daisy-chained to the UPS for even longer extended run operation
- Includes heavy gauge cabling with high current DC connectors for simple installation

Specifications

BATTERY	
Expandable battery runtime	Includes a second input/output connector to daisy-chain multiple battery packs
DC system voltage (VDC)	240
Connects to UPS via	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical battery lifespan	4-6 years typical (North America)
PHYSICAL	
Shipping weight (lbs)	176
Shipping weight (kg)	79.83
Unit Dimensions (HWD/in)	5.25 x 17.5 x 22.5
Unit Dimensions (HWD/cm)	13.34 x 44.45 x 57.15
Unit weight (lbs)	152.5
Unit weight (kg)	69.17
Material of construction	Black steel cabinet
Form factors supported	3U rack/tower
CERTIFICATIONS	
Certifications	Tested to UL, cUL, CE, NOM
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	WEXT3-BP240V10	3-Year Extended Warranty - For BP240V10RT3U	1
Extended Warranties	WEXT5-BP240V10	5-Year Extended Warranty - For BP240V10RT3U	1
Rackmount/Wallmount Kits	2POSTRMKITHD	Enables 2-Post Rackmount Installation of 3U and Larger UPS, Transformer and Battery Pack Components	1
Tower Stands	2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2491.

