

External Battery Pack for UPS System - NAFTA assembled version of BP48V60RT-3U

MODEL NUMBER: BP48V60-3UNAFTA



Highlights

- Extends runtime of select compatible Tripp Lite UPS Systems with 48VDC external battery connector
- Provides daisy-chain capability
- Simple installation; 3U rackmount, tower and stack adaptable

Package Includes

- BP48V60-3UNAFTA external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Description

BP48V60-3UNAFTA rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite systems. Multi-use form factor supports configuration in stacking, upright tower and rackmount applications using only 3 rack spaces (3U). Includes heavy gauge cabling with high current DC connector for simple installation. Additional output connector allows multiple BP48V60-3UNAFTA battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SM2200RMNAFTA, SM3000RMNAFTA, and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 3 rack spaces (3U)
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Additional output connector allows multiple BP48V60RT3U battery packs to be daisy-chained to the UPS for even longer extended run operation

Specifications

OVERVIEW	
UPC Code	037332137746
BATTERY	
Expandable Runtime	Yes
Expandable Runtime Description	Blue 2-point battery connector
DC System Voltage (VDC)	48
UPS Connection	Blue 2-point battery connector



Powering Business Worldwide



Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Form Factors Supported	3U rack/tower
Shipping Dimensions (hwd / in.)	11.25 x 23.00 x 31.50
Shipping Dimensions (hwd / cm)	28.58 x 58.42 x 80.01
Shipping Weight (lbs.)	202.83
Shipping Weight (kg)	92.00
Unit Dimensions (hwd / in.)	5.250 x 17.250 x 25.000
Unit Dimensions (hwd / cm)	13.3 x 44.4 x 63.5
Unit Weight (lbs.)	163.1
Unit Weight (kg)	73.98
ENVIRONMENTAL	
Operating Temperature	32-104 degrees F / 0-40 degrees C
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.