



Powering Business Worldwide

Network Surge Protector - Essential protection for data and communication lines

MODEL NUMBER: DB25-PAR



Highlights

- Complete serial port (DB25) surge protection
- Protects against the effects of electrostatic discharge
- Lifetime product warranty
- Heavy duty grounding lead

Package Includes

- DB25-PAR dataline protector
- Instruction manual and warranty information

Description

Tripp Lite's DB25-PAR offers dataline surge suppression for many DB25 parallel ports. Protects pins 1-25 and D shell chassis for protection of parallel DB25 ports. User configurable for use with male or female captive DB25 ports. Convenient DB25 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Tripp Lite network surge suppressors reduce blown interface connections, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground. Lifetime warranty.

SUPPRESSION: Reversible DB25 m/f jacks, protects pins 1-25 and chassis, 7.5V clamping

Features

- DB25-PAR protects 25 pin parallel ports using DB25 connections
- Protects pins 1-25 and D shell chassis for protection of parallel applications.
- User configurable for use with male or female captive DB25 port
- Convenient DB25 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis
- Offers protection on all 25 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground
- Lifetime product warranty

Specifications

OVERVIEW	
UPC Code	037332011008
INPUT	
Recommended Electrical Service	120V, 230V



Powering Business Worldwide

Input Plug Type	DB25
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	Hardwire
Circuit Breaker (amps)	750
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-25 & Chassis
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	



Powering Business Worldwide

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.