



# DataShield In-Line Surge Protector for Network and Digital/Leased Lines, T-1, ISDN, 1-Set RJ11/45/48

MODEL NUMBER: DSUT1CSU



Ideal for sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment.

#### **Description**

The DSUT1CSU offers complete surge suppression for equipment on digital and leased lines, T1 and ISDN interfaces. Ideal for the protection of sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment. Convenient eight-position input/output RJ-style jacks are RJ11/45/48 compatible, includes five-inch Ethernet cable for convenient placement at the protected device network connection. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. This network surge suppressors reduces blown interface ports, garbled network transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

### **Features**

- DSUT1CSU offers full surge suppression for CSU/DSU's and other high speed equipment on digital and leased lines, T1 and ISDN interfaces
- Convenient RJ45 input and output connections make for simple installation (RJ45 input/output connections, pins 1-8, 60V clamping)
- 5 inch ethernet patch cable enables ideal protection placed as close as possible to the point of use
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

# **Specifications**

OVERVIEW		
UPC Code	037332010872	
INPUT		
Nominal Input Voltage(s) Supported	120V AC; 230V AC	

## **Highlights**

- Complete T1 and ISDN (RJ11/45/48) surge protection
- Protects against the effects of electrostatic discharge

## **Package Includes**

- DSUT1CSU dataline protector
- 5 inch RJ45 patch cable
- Instruction manual and warranty information





December ded Electrical Comica	4001/ 2001/	
Recommended Electrical Service	120V, 230V	
Input Plug Type	RJ45	
Input Cord Length (ft.)	0	
Right-Angle Plug	No .	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
OUTPUT		
Output Receptacles	(1) Network	
Circuit Breaker (amps)	200	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	No	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	0	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	Yes	
Additional Dataline Protection	1-8	
Telephone/DSL Protection	No	
PHYSICAL		
Housing Color	Light Gray	
Mounting Holes or Slots	No	
Shipping Dimensions (hwd / in.)	6.10 x 2.00 x 3.10	
Shipping Dimensions (hwd / cm)	15.49 x 5.08 x 7.87	
Shipping Weight (lbs.)	0.20	
Shipping Weight (kg)	0.09	
Unit Dimensions (hwd / in.)	0.890 x 1.000 x 3.570	
Unit Weight (lbs.)	0.087	
Unit Weight (kg)	0.04	
COMMUNICATIONS		
Network Compatibility	100 Mbps (Fast Ethernet)	
· · ·		





FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.