



DataShield In-Line Surge Protector for Network and Phone Lines, 2-Line RJ11/RJ45

MODEL NUMBER: DTEL2



Protects up to 2 network or phone lines, modems, fax machines and answering machines against damage from electrostatic discharge and ground surges.

Description

DTEL2 surge suppressor is designed to protect data and communications equipment against AC transients caused by electrostatic discharge and ground surges that can enter equipment from the signal lines or chassis ground. The DTEL2 features RJ45/RJ11 plugs for modems, telephone lines and answering or fax machines.

Features

- Protects against the effects of electrostatic discharge
- Comes with RJ11 telephone patch cable

Specifications

OVERVIEW	
UPC Code	037332010865
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Plug Type	RJ11; RJ45
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No

Highlights

- RJ11/RJ45 2-line dial-up surge protector
- Protects against the effects of electrostatic discharge

Package Includes

- DTEL2 dataline protector
- 5-in. RJ11 telephone patch cable
- Warranty information and instruction manual



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	250
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	4,5 & 3,6 pairs
Telephone/DSL Protection	Yes
PHYSICAL	
Housing Color	Beige
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	5.20 x 3.00 x 2.10
Shipping Dimensions (hwd / cm)	13.21 x 7.62 x 5.33
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	3.500 x 1.000 x 1.000
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.