

Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SE



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM1327SE Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be adjusted for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 33 lbs (14.9 kgs).

Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 13 to 27 in. Ideal for home, office, hotels, bars and restaurants Full-motion swivel arm adjusts for angle Mounting hardware included

Convenient One-Touch Adjustment 180° swivel and -15° to +15° tilt capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 33 lbs (14.9 kgs) Scratch-resistant powder-coated finish blends with any décor Fully assembled for immediate installation

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332183514 |

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 33 lbs (14.9 kgs)

Package Includes

- DWM1327SE Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Anchor bolts
- (4) Concrete anchors
- Hex key, 4 mm
- Hex key, 5 mm
- Owner's manual



Powering Business Worldwide



| | |
|--------------------------------------|--------------------------|
| Device Compatibility | Monitor/HDTV |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Steel |
| VESA Pattern (mm) | 75x75; 100x100 |
| Motion | Full |
| Mounting Location | Wall |
| Degrees of Motion | -15/+15 Tilt; 180 Swivel |
| Minimum Screen Size (in.) | 13 |
| Minimum Screen Size (cm) | 33.02 |
| Maximum Screen Size (in.) | 27 |
| Maximum Screen Size (cm) | 68.58 |
| Maximum Weight Capacity (lbs.) | 33 |
| Maximum Weight Capacity (kg) | 15 |
| Min/Max Arm Extension (in.) | 4.14 min to 15.95 max |
| Min/Max Arm Extension (cm) | 10.5 min to 40 max |
| Number of Displays | 1 |
| Shipping Dimensions (hwd / in.) | 9.40 x 2.80 x 11.00 |
| Shipping Dimensions (hwd / cm) | 23.88 x 7.11 x 27.94 |
| Shipping Weight (lbs.) | 2.75 |
| Shipping Weight (kg) | 1.25 |
| Unit Dimensions (hwd / in.) | 8.260 x 4.600 x 16.000 |
| Unit Dimensions (hwd / cm) | 21.0 x 40.49 x 11.7 |
| Unit Weight (lbs.) | 2.66 |
| Unit Weight (kg) | 1.21 |
| FEATURES & SPECIFICATIONS | |
| Antimicrobial | No |
| Cord Management | No |
| Tools Necessary | Yes |
| Security Lock | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; RoHS3; REACH |
| WARRANTY & SUPPORT | |



Powering Business Worldwide



| | |
|--|-------------------------|
| Product Warranty Period (Worldwide) | 5-year limited warranty |
|--|-------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.