

Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SE



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM1327SE Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be adjusted for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 33 lbs (14.9 kgs).

Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Your TV or Monitor to the WallFits most flat-panel televisions, monitors and other displays from 13 to 27 in.Ideal for home, office, hotels, bars and restaurantsFull-motion swivel arm adjusts for angleMounting hardware included

Convenient One-Touch Adjustment180° swivel and -15° to +15° tilt capability provides comfortable viewing from multiple angles

Durable Metal ConstructionSupports up to 33 lbs (14.9 kgs)Scratch-resistant powder-coated finish blends with any décorFully assembled for immediate installation

VESA ComplianceSupports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 33 lbs (14.9 kgs)

Package Includes

- DWM1327SE Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Anchor bolts
- (4) Concrete anchors
- Hex key, 4 mm
- Hex key, 5 mm
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332183514



Powering Business Worldwide



Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Min/Max Arm Extension (in.)	4.14 min to 15.95 max
Min/Max Arm Extension (cm)	10.5 min to 40 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	9.40 x 2.80 x 11.00
Shipping Dimensions (hwd / cm)	23.88 x 7.11 x 27.94
Shipping Weight (lbs.)	2.75
Shipping Weight (kg)	1.25
Unit Dimensions (hwd / in.)	8.260 x 4.600 x 16.000
Unit Dimensions (hwd / cm)	21.0 x 40.49 x 11.7
Unit Weight (lbs.)	2.66
Unit Weight (kg)	1.21
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.