

Swivel/Tilt Wall Mount for 26" to 55" TVs and Monitors

MODEL NUMBER: DWM2655M



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM2655M Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 26 to 55 inches. Adjust the display's viewing angle to fit your environment and comfort level. A 120° swivel, -15° to +15° tilt and -5° to +5° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 110 lbs (49.9 kgs). Mounting hardware included. Built-in bubble level allows accurate display leveling. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 26 to 55 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants Viewing angle adjusts to fit your environment and comfort level Mounting hardware included

Convenient One-Touch Adjustment 120° swivel, -15° to +15° tilt and -5° to +5° screen level adjustment capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 110 lbs (49.9 kgs) Scratch-resistant powder-coated finish blends with any décor Built-in bubble level allows accurate display leveling

VESA Compliance Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm

Highlights

- Fits most flat-panel displays from 26 to 55 in.
- One-touch adjustment for comfortable viewing
- 120° swivel, -15° to +15° tilt and -5° to +5° screen adjustment
- Supports up to 110 lbs (49.9 kgs)

Package Includes

- DWM2655M Swivel/Tilt Wall Mount for 26" to 55" TVs and Monitors
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

UPC Code	037332183637
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 120 Swivel; -5/+5 Level Adjustment
Minimum Screen Size (in.)	26
Minimum Screen Size (cm)	66.04
Maximum Screen Size (in.)	55
Maximum Screen Size (cm)	139.7
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Min/Max Arm Extension (in.)	4.92 min to 20.27 max
Min/Max Arm Extension (cm)	12.5 min to 51.5 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	4.60 x 21.90 x 9.20
Shipping Dimensions (hwd / cm)	11.68 x 55.63 x 23.37
Shipping Weight (lbs.)	19.06
Shipping Weight (kg)	8.65
Unit Dimensions (hwd / in.)	7.670 x 16.850 x 16.850
Unit Dimensions (hwd / cm)	20.32 x 51.5 x 19.5
Unit Weight (lbs.)	18.45
Unit Weight (kg)	8.37
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.