



Easy Pull Long-Run Display Cable - Type-A Analog Plenum Trunk Cable, 35 ft. (10.67 m)

MODEL NUMBER: EZA-035-P



Highlights

- Versatile trunk cable allows for a variety of connection options
- Plenum-rated jacket to comply with local fire codes
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

Package Includes

 Easy Pull Type-A VGA Analog Plenum Trunk Cable, 35 ft.

Features

- Eliminates the need to field terminate VGA connectors
- Plenum-rated jacket to comply with local fire codes
- Detachable, screw-on connectors
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

Specifications

OVERVIEW		
UPC Code	037332141873	
Technology	VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
CONNECTIONS		
Side A - Connector 1	DIN 14 PIN (FEMALE)	
Side B - Connector 1	DIN 14 PIN (FEMALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black; Green	





Cable Jacket Color	Black; Green	
Cable Length (ft.)	35	
Cable Length (m)	10.67	
Shipping Dimensions (hwd / in.)	1.00 x 8.00 x 8.00	
Shipping Dimensions (hwd / cm)	2.54 x 20.32 x 20.32	
Shipping Weight (lbs.)	1.90	
Shipping Weight (kg)	0.86	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.