

Easy Pull Long-Run Display Cable - Type-A Analog PVC Trunk Cable, 50-ft.

MODEL NUMBER: EZA-050



Highlights

- Versatile trunk cable allows for a variety of connection options
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

Package Includes

- Easy Pull Type-A VGA Analog PVC Trunk Cable, 50 ft.

Description

Tripp Lite's EZA-050 50 ft. Easy Pull VGA Trunk cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35 ft., 50 ft., and 100 ft. lengths, both PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332141897 |
| Technology | VGA/SVGA |



Powering Business Worldwide



| CONNECTIONS | |
|-------------------------------------|---------------------------|
| Side A - Connector 1 | DIN 14 PIN (FEMALE) |
| Side B - Connector 1 | DIN 14 PIN (FEMALE) |
| Latching or Gripping Connector | No |
| PHYSICAL | |
| Color | Black; Green |
| Cable Length (ft.) | 50 |
| Cable Length (m) | 15.24 |
| Shipping Dimensions (hwd / in.) | 2.00 x 6.10 x 9.90 |
| Shipping Dimensions (hwd / cm) | 5.08 x 15.49 x 25.15 |
| Shipping Weight (lbs.) | 2.20 |
| Shipping Weight (kg) | 1.00 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.