

Easy Pull Long-Run Display Cable - Type-A Analog Plenum Trunk Cable, 50-ft.

MODEL NUMBER: EZA-050-P



Highlights

- Versatile trunk cable allows for a variety of connection options
- Plenum-rated jacket to comply with local fire codes
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

Package Includes

- Easy Pull Type-A VGA Analog Plenum Trunk Cable, 50 ft.

Description

Tripp Lite's EZA-050-P 50 ft. Easy Pull VGA Plenum Trunk Cable makes pulling video cable through conduit or confined areas a breeze. Plenum-rated jacket complies with local fire codes. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connectors
- Plenum-rated jacket complies to local fire codes
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35 ft., 50 ft. and 100 ft., both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

Specifications

OVERVIEW	
UPC Code	037332141866
Technology	VGA/SVGA



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	50
Cable Length (m)	15.24
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	4.50
Shipping Weight (kg)	2.04
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.