

# Easy Pull Long-Run Display Cable - Type-A Analog PVC Trunk Cable, 100 ft. (30.5 m)

MODEL NUMBER: EZA-100



### Highlights

- Versatile trunk cable allows for a variety of connection options
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

### Package Includes

- Easy Pull Type-A VGA Analog PVC Trunk Cable, 100-ft. (30.5 m)

### Description

Tripp Lite's EZA-100 100-ft. (30.5 m) Easy Pull VGA Trunk cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35-ft. (10.67 m), 50-ft. (15.24 m), and 100-ft. (30.5 m) lengths, PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

### Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35-ft. (10.67 m), 50-ft. (15.24 m), and 100-ft. (30.5 m) lengths, both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

## Specifications

OVERVIEW	
UPC Code	037332141880
Technology	VGA/SVGA



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	100
Cable Length (m)	30.49
Shipping Dimensions (hwd / in.)	2.00 x 9.50 x 10.00
Shipping Dimensions (hwd / cm)	5.08 x 24.13 x 25.40
Shipping Weight (lbs.)	3.90
Shipping Weight (kg)	1.77
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.