

# Easy Pull Type-A Connectors - (M/M set of VGA with Audio)

MODEL NUMBER: EZA-VGAAM-2



### Highlights

- SVGA / 3.5mm Stereo Connector Kit, Male to Male
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

### Package Includes

- 2 x HD15 Male/3.5mm Stereo Male, 1 ft. pigtails

### Description

Easy Pull Connector Kit includes: 2 x HD15 Male w/stereo 3.5mm plug, 1 ft. pigtails. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

### Features

- Easy Pull, 2 x HD15 Male & 2 x 3.5mm Stereo, 1 ft. pigtails
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- Support resolutions up to 1600 x 1200

## Specifications

OVERVIEW	
UPC Code	037332141958
Technology	VGA/SVGA; Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side A - Connector 3	DIN 14 PIN (MALE)
Side B - Connector 1	HD15 (MALE)



Powering Business Worldwide



Side B - Connector 2	3.5MM (MALE)
Side B - Connector 3	DIN 14 PIN (MALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black; Green
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	0.50 x 5.90 x 8.40
Shipping Dimensions (hwd / cm)	1.27 x 14.99 x 21.34
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.