

# Easy Pull Type-A Connectors - (M/F set of VGA with Audio and Faceplate)

MODEL NUMBER: EZA-VGAAX-2



### Highlights

- SVGA / 3.5mm Stereo Connector Kit, Male to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

### Package Includes

- HD15 Male w/stereo 3.5mm plug, 1 ft. pigtail
- HD15 Female w/stereo 3.5mm socket, 1 ft. pigtail
- Wall plate w/HD15 and 3.5mm cutouts

### Description

Easy Pull Connector Kit includes: HD15 Male w/stereo 3.5mm plug - 1 ft. pigtail, HD15 Female w/stereo 3.5mm socket - 1 ft. pigtail, and mounting wall plate. Completes your Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

### Features

- Eliminates the need to field terminate VGA connectors
- Wall Plate with HD15 and 3.5mm stereo cut-outs cleanly finish off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

## Specifications

OVERVIEW	
UPC Code	037332141965
Technology	VGA/SVGA; Stereo Audio
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side A - Connector 3	DIN 14 PIN (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	3.5MM (FEMALE)



Powering Business Worldwide



Side B - Connector 3	DIN 14 PIN (MALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black; Green
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.