



# Easy Pull Type-A Connectors - M/M set of VGA

MODEL NUMBER: EZA-VGAM-2



#### **Highlights**

- SVGA Connector Kit includes: Male to Male HD15 1 ft. (0.31 m) pigtail cables
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200
- Works in tandem with EZA-Series Cables

## **Package Includes**

• 2 x HD15 Male 1-ft. (0.31 m) pigtail cable

#### **Description**

Easy Pull Connector Kit includes: 2 x HD15 Male 1-ft. (0.31 m) pigtail cable. Completes your Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

### **Features**

- Eliminates the need to field terminate VGA connectors
- Wall plate with HD15 cut-out cleanly finish off the cable run
- Allows cable to be run according to code inside conduit, drop ceilings, etc.
- · Makes pulling long cables fast and easy
- Trunk cables available in 35-ft. (10.67 m), 50-ft. (15.24 m) and 100-ft. (30.5 m) PVC lengths, and 35-ft. (10.67 m) and 50-ft. (15.24 m) Plenum jackets
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

# **Specifications**

OVERVIEW		
UPC Code	037332142016	
Product Type	Passive Cable	
Technology	VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	
Side A - Connector 2	DIN 14 PIN (FEMALE)	
Side B - Connector 1	HD15 (MALE)	





Side B - Connector 2	DIN 14 PIN (FEMALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black; Green	
Cable Jacket Color	Black; Green	
Cable Length (ft.)	1	
Cable Length (m)	0.30	
Cable Length (in.)	12	
Shipping Dimensions (hwd / in.)	0.25 x 1.00 x 12.00	
Shipping Dimensions (hwd / cm)	0.64 x 2.54 x 30.48	
Shipping Weight (lbs.)	0.40	
Shipping Weight (kg)	0.18	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
	-	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.