



Easy Pull Long-Run Display Cable - Type-B Digital PVC Trunk Cable, 100 ft. (30.5 m)

MODEL NUMBER: EZB-100



Highlights

- Versatile trunk cable allows for a variety of connection options
- Easily pulls through conduit or confined spaces with included end caps with integrated pull tabs
- UL20276 Digital Video Cable supports 1080i
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Package Includes

 Easy Pull Type-B Digital PVC Trunk Cable, 100-ft. (30.5 m)

Description

Tripp Lite's EZB-100 100-ft. (30.5 m) Easy Pull Digital Trunk cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from HDMI and DVI termination kits that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 50-ft. (15.24 m) and 100-ft. (30.5 m) PVC (Plenum available as custom item). Cable ends are colored-coded yellow to denote Digital applications (VGA trunk cables are green). Cable features 4pr UL20276 individually shielded twisted pairs, one twisted pair and five signal conductors. UL20276 Digital Video Cable supports 1080i.

Features

- · Eliminates the need to field terminate HDMI and DVI connectors
- · Detachable, screw-on connectors
- Allows cable to be run according to code inside conduit, drop ceilings, etc.
- · Makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 50-ft. (15.24 m) and 100-ft. (30.5 m) PVC lengths (Plenum cables available upon request)
- UL20276 Digital Video Cable supports 1080i
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Specifications

OVERVIEW	
UPC Code	037332141859
Technology	DVI; HDMI





CONNECTIONS		
Side A - Connector 1	DIN 19 PIN (FEMALE)	
Side B - Connector 1	DIN 19 PIN (FEMALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black; Yellow	
Cable Length (ft.)	100	
Cable Length (m)	30.49	
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 0.50	
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 1.27	
Shipping Weight (lbs.)	4.64	
Shipping Weight (kg)	2.11	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.