



Powering Business Worldwide

FireWire IEEE 1394 Cable (6pin/4pin M/M) 15-ft.

MODEL NUMBER: F007-015



Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity

System Requirements

- Firewire 1394 device with a 6-Pin connector and a Firewire device with a 4-Pin connector

Package Includes

- 15-ft. Firewire IEEE 1394 6Pin/4Pin with Gold Connectors

Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. This 15Ft. IEEE-1394 Firewire cable has 6-pin male to 4-pin male connectors supports data transmission of 100~400Mbps and used most commonly to connect a PC device to an A/V device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference.

Features

- All Tripp Lite Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps

Specifications

OVERVIEW	
UPC Code	037332012029
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	4 PIN (MALE)
PHYSICAL	
Color	Black

Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.36
Shipping Weight (kg)	0.16
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.