



Powering Business Worldwide

FireWire IEEE 1394 Cable (4pin/4pin M/M) 6-ft.

MODEL NUMBER: F009-006



Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Supports data transfer rates up to 400Mbps
- Gold plated connectors provide superior conductivity

Package Includes

- 6 ft. IEEE 1394 Firewire 4-pin to 4-pin. cable with Gold connectors

Description

Tripp Lite's 6 ft. IEEE 1394 Firewire 4-pin to 4-pin cable supports data transfer rates up to 400Mbps, and features both gold-plated contacts and connectors for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference.

Features

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole.
- Supports data transfer rates up to 400Mbps.
- Gold plated connectors provide superior conductivity.

Specifications

OVERVIEW	
UPC Code	037332012036
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	4 PIN (MALE)
Side B - Connector 1	4 PIN (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83



Powering Business Worldwide

Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.