

FireWire 800 IEEE 1394b Hi-speed Cable (9pin/6pin M/M) 10 ft. (3.05 m)

MODEL NUMBER: F017-010



Highlights

- Connects Firewire 800 devices to legacy 1394a ports
- Meets FireWire 800 and 1394b Specifications
- Backward compatible to Original FireWire components

Package Includes

- 10-ft. (3.05 m) IEEE-1394b FireWire 800 Gold Hi-Speed 9pin/6pin Cable

Features

- Data transfer rates to 800Mbps
- Hot Pluggable - supports Plug-n-Play operation
- Premium triple-shielded cable with molded, Gold connectors
- Backward compatible with FireWire systems and devices
- Compatible with PC, Mac, SUN, and other IEEE-1394b equipped systems

Specifications

OVERVIEW	
UPC Code	037332124593
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	9 PIN (MALE)
Side B - Connector 1	6 PIN (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	0.25 x 6.10 x 7.60



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	0.64 x 15.49 x 19.30
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.