



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: HT2210ISOCTR

Low-profile power center designed for flat-panel TVs, rear-screen projection System and more - Isobar Audio/Video Power Center



Highlights

- 2 surge/spike protected AC outlets
- 5100 joules surge suppression rating
- 1-line HD 2.2 GHz (gold) coaxial surge protection
- 1-Network/Ethernet protection with RJ45
- 3 Diagnostic LEDs report operational conditions
- 10 ft. and 18 in. detachable power cords with right-angle plugs
- All-metal housing within a Low profile design provides additional EMI/RFI rejection
- \$100,000 [Ultimate Lifetime Insurance](#) (USA/Canada only); lifetime product warranty

Description

Tripp Lite's HT2210ISOCTR Isobar Audio/Video Power Center provides ultimate protection - 5100 joules - stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for flat-panel TVs, rear-screen projection systems and more. Premium Isobar surge protection technology. Low-profile design that fits neatly behind flat panel TV's. HD 2.2 GHz (gold) coaxial protects against surges from coming in on the coax input. Ethernet protection with RJ45 protects from surges coming in on the network. All-metal housing, 2 AC outlets, 3 diagnostic LEDs, 10-ft and 18-in. detachable cords with right-angle plugs, 24K gold plug contacts, circuit breaker, fail-safe thermal fusing and audible alarm. Remote AC/DC control jack allows remote on/off control from an external component. Includes mounting brackets. \$100,000 Ultimate Lifetime Insurance coverage (USA/Canada only); lifetime product warranty

Applications

- Ideal for flat panel TVs and rear-screen projection systems

Package Includes

- HT2210ISOCTR Audio/Video Power Center
- Mounting brackets
- Instruction manual with warranty information
- 1 Coax Cable
- 1 RJ45 Network Cable

Features

- 5100 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Rugged all-metal housing safely withstands the strongest surges
- 2 surge/spike protected NEMA 5-15R AC outlets
- 10-ft. and 18-in. detachable cords with right-angle NEMA 5-15P plugs enable convenient placement anywhere within a home/business theater system.

- 1-line HD2.2 GHz (gold) coaxial surge protection
- 1-Network/Ethernet protection with RJ45
- 3 diagnostic LEDs (LINE OK, GROUND OK & SURGE OK)
- Included brackets enable convenient mounting behind any flat-panel TV
- Illuminated master switch provides one-touch power control over all components
- Circuit breaker protects against dangerous system overload
- TUV tested to UL standards 1449 and 962A
- Fail-safe thermal fusing acts like an additional circuit breaker, shutting down the unit and connected equipment during a catastrophic surge
- Audible alarm immediately alerts you to damaged protection circuitry, perfect for when LEDs aren't normally viewed
- 24k gold plug contacts resist corrosion to improve AC power flow
- Remote AC/DC control jack permits remote on/off control from an external component
- \$100,000 [Ultimate Lifetime Insurance](#) (USA/Canada only) covers connected components against surge damage—for life!
- Lifetime product warranty

Specifications

OVERVIEW	
Intended Application	Audio/Video
SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1440
Output volt amp capacity (amps)	12
Overload protection	12-amp circuit breaker
Outlet quantity / type	2 NEMA 5-15R
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	Detachable NEMA 5-15P
Input plug features	Right-angle plug with 24k gold contacts
Input cord length (ft.)	10 ft. and 18 in.
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Alarms	Audible alarm
Switches	On/Off power switch and circuit breaker switch
Diagnostic LEDs	3
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	5100 joules
AC suppression response time	NM = instantaneous CM = < 1 ns
Safe thermal fusing	Yes
UL1499 let through rating	330V - UL verified

EMI / RFI filtering	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	Yes
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping weight (lbs)	2.8
Unit weight (lbs)	2.6
Material of construction	Metal
Mounting accessories included	Mounting brackets
Receptacle Color	Black
AC line cord color	Black
Style	Low Profile
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
Approvals	RoHS, TUV tested to UL standards 1449 & 962A
WARRANTY	
Standard warranty period	Lifetime
Connected equipment insurance (USA, Canada, Puerto Rico)	\$100,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3499.