

Isobar Home/Business Theater Surge Suppressor - Ultimate-performance surge and line noise protection for all components

MODEL NUMBER: HTPOWERBAR10



Highlights

- 10 outlets / 8-ft. cord
- 5700 joule rating
- Isolated Filter Banks / metal housing
- 3-line coaxial (gold) surge protection
- 1-line tel/modem surge protection
- \$500,000 Ultimate Lifetime Insurance (USA and Canada only)

Package Includes

- HTPOWERBAR10 Home/Business Theater Surge Suppressor
- Two 6-ft. gold coaxial cables and 6-ft. phone cord
- Instruction manual with warranty information

Description

Tripp Lite's HTPOWERBAR10 Isobar Home/Business Theater Surge Suppressor provides ultimate protection--5700 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 10 outlets (with transformer spacing and plug-in safety covers), 3-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$500,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes metal housing, color-coordinated outlet/plug labels, 16 diagnostic LEDs, 8-ft. cord with a right-angle plug, two 6-ft. gold coaxial cables and 6-ft. phone cord.

Features

- 5700 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$500,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- Isolated Filter Banks eliminate interference between connected components
- Metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 6 transformers
- 4 plug-in safety covers protect against accidental contact
- 3 sets of surge-protected Type F gold coaxial connectors (with two included 6-ft. gold coaxial cables) safeguard components on cable, satellite and antenna line
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (PVRs) on a single dial-up line. Built-in splitter (1 jack in and 2 jacks out) allow simultaneous connection of two devices sharing a single line
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 16 diagnostic LEDs alert user to 6 input voltage levels, 6 amp usage levels and 4 operational conditions (protection, grounding, power, switched status)
- Keyhole slots provide convenient wall or cabinet mounting

- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- Metal housing (gold) stands up to the most demanding environments
- UL and cUL listed
- Lifetime product warranty
- Color-coordinated outlet/plug labels

Specifications

OVERVIEW	
UPC Code	037332263933
INPUT	
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LED Details	16 diagnostic LEDs alert user to 6 input voltage levels, 6 amp usage levels and 4 operational conditions (protection, grounding, power, switched status)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5700
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression



Powering Business Worldwide



UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Yes
Isolated Filter Banks	10
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Unit Dimensions (hwd / in.)	19.000 x 3.750 x 5.000
Unit Dimensions (hwd / cm)	48.3 x 9.5 x 12.7
Unit Weight (lbs.)	4.5
Unit Weight (kg)	2.04
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.