



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: INTERNET550U

### Internet Office 550VA Ultra-compact Standby 120V UPS with USB port



#### Highlights

- 550VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 4 UPS battery supported outlets, 4 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

#### Description

Tripp Lite's INTERNET550U standby UPS offers complete protection for PCs, workstations and other sensitive electronics in an attractive ultra-compact, mountable housing. Prevents data loss and system downtime by providing battery supported AC output during brownouts and blackout conditions. 8 output receptacles, two of which are widely-spaced to accommodate large transformer plugs without blocking outlets. 4 outlets with full battery support and surge suppression protect computers, monitors and other vital system components from loss of power. 4 additional outlets with surge suppression-only are ideal for printers and other accessories not requiring battery support. Single line telephone suppression jacks protect modem, fax machine, cordless phone or other peripherals with a standard dialup or DSL phone line connection. USB port with PowerAlert monitoring software (available via web download) and cabling enables safe unattended system shutdown in the case of extended power failure. HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X. Audible alarm and front panel LEDs offer status information regarding line and battery power operation. 550VA/300 watt power handling ability supports entry-level PCs for up to 17 minutes during power failures. \$100,000 [connected equipment insurance](#) (USA, Puerto Rico and Canada only).

#### Package Includes

- INTERNET550U UPS System
- USB cable
- Instruction manual with warranty information

#### Features

- INTERNET550U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and Tel/DSL line connections
- 8 outlets, two of which are widely spaced to accommodate large transformer plugs without blocking outlets
- 4 battery supported outlets protect computer, monitor and vital system peripherals, plus 4 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 550VA/300 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 17 minutes during blackout conditions
- Built-in single line Tel/DSL line surge suppression protects modem, fax machine or cordless phone
- USB port, PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages
- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.

- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Space saving, ultra-compact housing fits almost anywhere
- Keyhole mounting flanges enable secure wallmount installation

## Specifications

<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (watts)	300
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	8 5-15R outlet(s)
Surge suppression only outlets	4 UPS outlets, 4 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
Input circuit breaker	10A
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
<b>BATTERY</b>	
Full load runtime (minutes)	3.5 min. (300w)
Half load runtime (minutes)	10 minutes (150w)
DC system voltage (VDC)	12
<b>LEDS ALARMS &amp; SWITCHES</b>	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
<b>SURGE / NOISE SUPPRESSION</b>	

UPS AC suppression joule rating	420
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
<b>PHYSICAL</b>	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.1 x 5.7 x 10.8
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	7.8 x 14.6 x 27.6
UPS / Power Module weight (lbs)	6.5
UPS / Power Module weight (kg)	3
UPS Shipping dimensions (height x width x depth / inches)	4.1 x 8 x 13
UPS Shipping dimensions (height x width x depth / cm)	10.4 x 20.3 x 33
Shipping weight (lbs)	7
Shipping weight (kg)	3.2
UPS housing material	ABS
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	14
Battery mode BTU / hr. (full load)	194.3
<b>COMMUNICATIONS</b>	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications

<b>LINE / BATTERY TRANSFER</b>	
Transfer time	4 milliseconds (AC to battery mode) / 2 milliseconds (battery mode to AC)
Low voltage transfer to battery power (setpoint)	99
High voltage transfer to battery power (setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Product Warranty Period (Puerto Rico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a href="#">Ultimate Lifetime Insurance</a>

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Audio Cables	<a href="#">CT120</a>	Instant-Read- AC Outlet Circuit Tester	1
Extended Warranties	<a href="#">WEXT5-INTERNET</a>	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	1
Software	<a href="#">WATCHDOGSW</a>	WatchDog Service Monitoring / Reboot Software	1
Surge Protectors	<a href="#">DCATV</a>	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
Surge Protectors	<a href="#">DNET1</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
Surge Protectors	<a href="#">DTEL2</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
USB Cables & Adapters	<a href="#">U005-10I</a>	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	1
USB Hubs/Accessories	<a href="#">U222-004-R</a>	4-Port USB2.0 Ultra-Mini Hub	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3063](http://www.tripplite.com/en/products/model.cfm?txtModelID=3063).

---

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.