



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: INTERNET550U

Internet Office UPS System - Affordable full system protection for PCs and workstations

Highlights



- 550VA ultra-compact UPS
- Maintains 120V nominal output during blackouts
- Workstation optimized features include USB port (HID-PDC compliant), single line TEL / DSL surge suppression and four surge-only outlets
- 99% line-mode efficiency saves energy and operating costs
- Input: NEMA 5-15P (120V 15A) / Output: 8 NEMA 5-15R (120V)
- 3 year product warranty / \$100,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's INTERNET550U standby UPS offers complete protection for PCs, workstations and other sensitive electronics in an attractive ultra-compact, mountable housing. Prevents data loss and system downtime by providing battery supported AC output during brownouts and blackout conditions. 8 output receptacles, two of which are widely-spaced to accommodate large transformer plugs without blocking outlets. 4 outlets with full battery support and surge suppression protect computers, monitors and other vital system components from loss of power. 4 additional outlets with surge suppression-only are ideal for printers and other accessories not requiring battery support. Single line telephone suppression jacks protect modem, fax machine, cordless phone or other peripherals with a standard dialup or DSL phone line connection. USB port with PowerAlert monitoring software (available via web download) and cabling enables safe unattended system shutdown in the case of extended power failure. HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X. Audible alarm and front panel LEDs offer status information regarding line and battery power operation. 550VA/300 watt power handling ability supports entry-level PCs for up to 17 minutes during power failures. 3 year warranty. \$100,000 [connected equipment insurance](#) (USA, Puerto Rico & Canada Only).

Package Includes

- INTERNET550U UPS System
- USB cable
- Instruction manual with warranty information

Features

- INTERNET550U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and Tel/DSL line connections
- 8 outlets, two of which are widely spaced to accommodate large transformer plugs without blocking outlets
- 4 battery supported outlets protect computer, monitor and vital system peripherals, plus 4 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 550VA/300 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 17 minutes during blackout conditions
- Built-in single line Tel/DSL line surge suppression protects modem, fax machine or cordless phone
- USB port, PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages

- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Space saving, ultra-compact housing fits almost anywhere
- Keyhole mounting flanges enable secure wallmount installation

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (watts)	300
Nominal Output Voltage(s) Supported	115v; 120v
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	8 5-15R outlet(s)
Surge suppression only outlets	4 UPS outlets, 4 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Space saving right angled input plug
Input circuit breaker	10A
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	3.5 min. (300w)
Half load runtime (minutes)	10 minutes (150w)
DC system voltage	12V DC

Battery recharge rate (included batteries)	Less than 15 hours from 10% to 90%
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	420
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL / DSL protection (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.1 x 5.7 x 10.8
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	7.8 x 14.6 x 27.6
Installed whole system dimensions in secondary form factor (height x width x depth / inches)	
UPS dimensions in secondary form factor (height x width x depth / cm)	
UPS / Power Module weight (lbs)	6.5
UPS / Power Module weight (kg)	3
Stepdown transformer dimensions (height x width x depth / inches)	
Stepdown transformer dimensions (height x width x depth / cm)	
Included battery pack dimensions (height x width x depth / inches)	

Included battery pack dimensions (height x width x depth / cm)	
UPS Shipping dimensions (height x width x depth / inches)	4.1 x 8 x 13
UPS Shipping dimensions (height x width x depth / cm)	10.4 x 20.3 x 33
Shipping weight (lbs)	7
Shipping weight (kg)	3.2
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	10.3
Battery mode BTU / hr. (full load)	194.3
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from www.tripplite.com
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	99
High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications); ROHS (Reduction of Hazardous Substances)
WARRANTY	

Standard warranty period	3 years
Connected equipment insurance (USA, Canada, Puerto Rico)	\$100,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Audio Cables	CT120	Instant-Read- AC Outlet Circuit Tester	-
Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	-
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	-
USB Cables & Adapters	U005-10I	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	-
USB Hubs/Accessories	U222-004-R	4-Port USB2.0 Certified Ultra-Mini Hub	-
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	-
Extended Warranties	WEXT5-INTERNET	5-Year Extended Warranty - For Internet Office Models	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at

www.tripplite.com/en/products/model.cfm?txtModelID=3063.