



# 900VA 480W Standby UPS - 12 NEMA 5-15R Outlets, 120V, 50/60 Hz, 5-15P Plug, ENERGY STAR, Desktop/Wall

# MODEL NUMBER: INTERNET900U



Compact desktop UPS with silent alarm provides battery backup support for your home/office network system or digital signage components.

### **Features**

**Energy-Saving 900VA/480W/120V Battery Backup for PCs, Home Theater and Digital Signage**The standby INTERNET900U UPS system provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The 12-outlet 120V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, NAS drives, HDTVs, Blu-ray players, game consoles, media players, DVRs and audio receivers.

Allows Time to Back Up Critical Files During a Blackout Backup support allows you to work through short power failures and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the INTERNET900U should keep an energy-efficient desktop computer with small LCD monitor powered as long as 41 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

**12 NEMA 5-15R Outlets Protect Your Connected Components**Six 5-15R outlets provide battery backup and surge protection for your computer, monitor and other crucial components. The other six 5-15R outlets provide surge suppression only for printers, speakers and other desktop equipment regarded as non-essential during a blackout.

**ENERGY STAR-Certified to Help You Save Money and Protect the Environment**By meeting strict EPA efficiency guidelines, this ENERGY STAR-certified UPS system helps you save money and energy. A high >98% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

**316 Joules Fight Back Against Unexpected Power Surges**A 316-joule surge suppression rating protects connected components from the harmful effects of power surges. Dual network data line surge suppression jacks protect a wired peripheral from dangerous surges on a single 10/100Base-T or dial-up network connection.

**HID-Compliant USB Port Allows for Automatic Saves and Shutdowns**This USB port connects the INTERNET900U to a computer running free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. USB cable is included.

## **Highlights**

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- 12 NEMA 5-15R outlets power and protect PC, home theater or digital signage equipment
- Home-friendly alarm remains silent in backup mode, sounding only when imperative
- ENERGY STAR-certified to save electricity, lower costs, and protect the environment

### **Applications**

- Protect your PC and other sensitive electronics against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Extend runtime for DVRs, wireless routers and other lowpower home network equipment

#### **Package Includes**

- INTERNET900U 900VA 480W 120V Standby UPS with 12 Outlets
- USB cable
- · Owner's manual



**Combats Electromagnetic Interference That Can Harm Equipment**Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The INTERNET900U incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

**Home-Friendly Alarm and Diagnostic LEDs Keep You Informed 24/7**The UPS remains silent in both line and battery backup modes. The alarm sounds only to warn you of a low battery or fault condition. Front-panel LEDs indicate operating mode, low- and replace-battery, overload and fault conditions.

**Compact Housing Compatible with Easy Desktop or Wall-Mount Installation**The space-saving ABS housing fits on a desktop, shelf or anywhere else convenient to your workstation or home theater. Keyhole mounting tabs on the rear allow easy wall-mount installation. The five-foot power cord with NEMA 5-15P plug connects to any compatible AC outlet.

# **Specifications**

OVERVIEW			
UPC Code	037332211095		
UPS Type	Standby		
INPUT			
Input Phase	Single-Phase		
Rated input current (Maximum Load)	10A		
Nominal Input Voltage(s) Supported	120V AC		
UPS Input Connection Type	5-15P		
Input Circuit Breakers	10A		
UPS Input Cord Length (ft.)	5		
UPS Input Cord Length (m)	1.5		
Recommended Electrical Service	15A 120V		
OUTPUT			
Output Capacity (VA)	900		
Output Capacity (kVA)	0.9		
Output Capacity (Watts)	480		
Output Capacity (kW)	0.48		
Output Capacity Details	7.5A @ 120V. 110%±10%,GOES TO FAULT AFTER 5MIN; 120%±10%,GOES TO FAULT IMMEDIATELY 110%±10%,SHUTS DOWN IN 5 SEC; 120%±10%, SHUTS DOWN IMMEDIATELY		
Power Factor	0.53		
Nominal Voltage Details	120V sinusoidal in line mode and 120V PWM in battery mode		
Frequency Compatibility	50 / 60 Hz		
Frequency Compatibility Details	Output is regulated to +/-0.05Hz when input frequency exceeds +/-5Hz of nominal.		





Output Voltage Regulation (Line Mode)	120V (±20%)	
Output Voltage Regulation (Battery Mode)	120V (±10%)	
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 6 surge-only outlets	
Output AC Waveform (AC Mode)	Pure sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	
Nominal Output Voltage(s) Supported	110V; 115V; 120V	
Output Receptacles	(12) 5-15R	
Individually Controllable Load Banks	No	
BATTERY		
Battery Type	Valve Regulated Lead Acid (VRLA)	
Runtime Full Load (min.)	1.7 min. (480W)	
Runtime Half Load (min.)	7.8 min. (240W)	
Expandable Runtime	No	
DC System Voltage (VDC)	12	
Battery Recharge Rate (Included Batteries)	8 hours (10% to 90%)	
Battery Access	Battery access door	
Internal UPS Replacement Battery Cartridge	IMPORTANT BATTERY REPLACEMENT INFORMATION > If your INTERNET900U has no battery access door, please contact a local electronics repair technician to source and install a matching replacement battery; If your INTERNET900U UPS does have a battery replacement door, please order Tripp Lite <a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-&lt;br&gt;other-UPS-RBC51">RBC51</a>	
Battery Replacement Description	Replaceable internal batteries (see manual)	
VOLTAGE REGULATION		
Voltage Regulation Description	Input voltage range of 95 to 145	
USER INTERFACE, ALERTS & CON	TROLS	
Switches	Switch controls power off/on status	
Audible Alarm	UPS remains silent in battery backup mode; Alarm sounds only to report low-battery, fault, overload and replace- battery conditions	
LED Indicators	Set of 3 status LEDs indicate operating mode, low-battery, overload, replace-battery and fault conditions	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	316	
UPS AC Suppression Response Time	Instantaneous	
UPS Dataline Suppression	1 line TEL/DSL or Ethernet	





EMI / RFI AC Noise Suppression	Yes	
PHYSICAL		
Primary Form Factor	Desktop	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop; Wallmount	
Primary UPS Depth (mm)	310	
Primary UPS Height (mm)	85	
Primary UPS Width (mm)	130	
Shipping Dimensions (hwd / in.)	7.83 x 5.98 x 14.92	
Shipping Dimensions (hwd / cm)	19.89 x 15.19 x 37.90	
Shipping Weight (lbs.)	8.10	
Shipping Weight (kg)	3.67	
UPS Housing Material	ABS	
UPS Power Module Dimensions (hwd, cm)	8.51 x 13.00 x 30.99	
UPS Power Module Dimensions (hwd, in.)	3.35 x 5.12 x 12.2	
UPS Power Module Weight (kg)	3.09	
UPS Power Module Weight (lbs.)	6.82	
Unit Weight (lbs.)	8.100	
Unit Weight (kg)	3.67	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	5° to 113°F (-15° to 45°C )	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	8.3	
AC Mode Efficiency Rating (100% Load)	>98%	
AC Economy Mode Efficiency Rating (100% Load)	>98%	
Operating Elevation	0-6562 ft. (0-2000 m)	
COMMUNICATIONS		
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert software at https://tripplite.eaton.com/products/power-alert	
Communications Cable	USB interface cable included	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Network Management Card		





Communications Interface	USB (HID enabled)		
LINE / BATTERY TRANSFER			
Transfer Time	6 milliseconds typical (10 milliseconds max)		
Low Voltage Transfer to Battery Power (Setpoint)	95		
High Voltage Transfer to Battery Power (Setpoint)	145		
FEATURES & SPECIFICATIONS			
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Surge/noise protection		
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS		
APPLICATIONS			
UPS Applications	Audio/Video; Retail/Point of Sale; Hospitality		
STANDARDS & COMPLIANCE			
Product Certifications	RETIE (Colombia); CSA (Canada); CAN/CSA-C22.2 No. 107.3 (Canada); NOM (Mexico); UL 1778		
Product Compliance	RoHS; ENERGY STAR Qualified; FCC Part 15 Class B (USA)		
WARRANTY & SUPPORT			
Product Warranty Period (U.S. & Canada)	3-year limited warranty		
Product Warranty Period (Latin America)	3-year limited warranty		
Product Warranty Period (International)	2-year limited warranty		
Product Warranty Period (Mexico)	3-year limited warranty		
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>		

1000 Eaton Boulevard

Cleveland, OH 44122

United States

https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.