

# 600VA 600W Line Conditioner - Automatic voltage regulation with surge protection

MODEL NUMBER: LS600

#### **Description**

Tripp Lite's LS600 automatic voltage regulation system offers complete protection from brownouts and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 120V nominal AC output during brownouts as low as 87V. Network grade equipment protection offers AC surge and noise suppression. Supports loads up to 600 watts. Includes 2 NEMA5-15R outlets, 6-ft. line cord and 1 LED that displays site power availability. \$10,000 Ultimate Lifetime Insurance (USA & Canada Only).

#### **Features**

- Maintains usable 120V nominal output during brownouts as low as 87V
- 600 watts output power rating supports 120V loads up to 5 amps
- Network grade surge suppression
- · Complete EMI/RFI noise filtering
- 3 diagnostic LEDs indicate input voltage status and surge suppression status
- 2 protected NEMA5-15R outlets
- 6-ft. AC power cord with standard NEMA5-15P input plug
- 2 year manufacturers product warranty
- \$10,000 Ultimate Lifetime connected equipment insurance (USA & Canada Only)

### **Highlights**

- Automatically adjusts low voltage
- 600 watts continuous
- 2 NEMA 5-15 R outlets
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### **Package Includes**

- LS600 Line Conditioner
- · Mounting hardware
- Instruction manual

## **Specifications**

OVERVIEW		
OVERVIEW		
UPC Code	037332040237	
INPUT		
Input Cord Length (ft.)	8	
Input Cord Length (m)	2.44	
OUTPUT		
Output Receptacles	(2) 5-15R	
Output Nominal Voltage	120v / 60Hz	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LEDs	1 LED indicates line power is present	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	240	
EMI / RFI AC Noise Suppression	20 dB	



PHYSICAL	
Material of Construction	Plastic
Form Factors Supported	Small Tower
Shipping Dimensions (hwd / in.)	5.31 x 8.75 x 8.75
Shipping Dimensions (hwd / cm)	13.49 x 22.22 x 22.22
Shipping Weight (lbs.)	4.50
Shipping Weight (kg)	2.04
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	14.6 x 10.8 x 13.34
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &hbsp

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.