



Powering Business Worldwide

600VA 600W Line Conditioner - Automatic voltage regulation with surge protection 4 Outlets

MODEL NUMBER: **LS604**

Description

Tripp Lite's LS604 automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 120V nominal AC output during brownouts as low as 87V and overvoltages to 140V. Network grade equipment protection offers AC surge and noise suppression. Supports loads up to 600 watts. Includes 4 NEMA5-15R outlets, 6-foot line cord and 3 diagnostic LEDs that display incoming voltage level, surge protection status and line fault conditions. \$10,000 Ultimate Lifetime Insurance (USA & Canada Only).

Features

- Maintains usable 120V nominal output during brownouts as low as 87V and overvoltages as high as 140V
- 600 watts output power rating supports 120V loads up to 5 amps
- Network grade surge suppression
- Complete EMI/RFI noise filtering
- 3 diagnostic LEDs indicate input voltage status and surge suppression status
- 4 protected NEMA5-15R outlets
- 6 ft. AC power cord with standard NEMA5-15P input plug
- 2 year manufacturers product warranty
- \$10,000 Ultimate Lifetime connected equipment insurance (USA & Canada Only)

Specifications

OVERVIEW	
UPC Code	037332040244
INPUT	
Input Cord Length (ft.)	9
Input Cord Length (m)	2.74
OUTPUT	
Output Nominal Voltage	120v / 60Hz
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	3 LEDs indicate incoming voltage status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	720
EMI / RFI AC Noise Suppression	20 dB

Highlights

- Automatically adjusts low or high voltage
- 600 watts continuous
- 4 NEMA 5-15R outlets
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Package Includes

- LS604 Line Conditioner
- Mounting hardware
- Instruction manual

PHYSICAL	
Material of Construction	Plastic
Form Factors Supported	Small Tower
Shipping Dimensions (hwd / in.)	8.50 x 8.75 x 5.50
Shipping Dimensions (hwd / cm)	21.59 x 22.22 x 13.97
Shipping Weight (lbs.)	4.77
Shipping Weight (kg)	2.16
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	14.6 x 10.8 x 13.34
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.